Heavy Duty Connector Inserts Combination



80A/16A, 400V/400V, 4 Pin/8 Pin, Insert

RoHS Compliant



Power Area Rated Current

Specifications

Rated Current : 80A
Rated Voltage : 400V
Rated Impulse Voltage : 6KV
Pollution Degree : 3

Signal Area

 $\begin{array}{lll} \mbox{Rated Current} & : 16\mbox{A} \\ \mbox{Rated Voltage} & : 400\mbox{V} \\ \mbox{Rated Impulse Voltage} & : 6\mbox{KV} \\ \mbox{Pollution Degree} & : 3 \\ \mbox{Insulation Resistance} & : \geq 10^{10}\mbox{\Omega} \\ \end{array}$

Material : Polycarbonate
Temperature Range : -40°C to +125°C

Mating Cycles : ≥500

Contact Material : Copper Alloy

Contact Surface : Silver plated / Gold plated Contact Resistance : $\leq 0.3 m\Omega$ (Power Area)

≤1mΩ (Signal Area)


Power Area


Wire Gauge : $1.5\sim16$ mm² AWG : 16-6

Signal Area

Wire Gauge : $0.5\sim2.5$ mm² AWG : 20-14

Diagram





Dimensions: Millimetres

Part Number Table

Description	Part Number
Heavy Duty Connector Insert, 80A/16A, 400V/400V, 4 Pin/8 Pin, Female, Screw Terminal	MP009600
Heavy Duty Connector Insert, 80A/16A, 400V/400V, 4 Pin/8 Pin, Male, Screw Terminal	MP009601

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

