Amphenol ^{Mfg by} EAXTRON Industrial UL 1977 Effortless & Arcless Din Connectors 160A/320A/430A

than normal for connecting and disconnecting

IB-16

EFFORTLESSNESS

Amphenol Industrial Operations (AIO) has partnered with Eaxtron who has designed a state of the art female contact. The patented Vortex Clip[™] significantly improves all aspects of the connection interface. Not only does the unique spiraling shape allow for more contact points, providing a higher rate of conductivity, it also facilitates coupling with eighty percent less effort than the industry standard!

DURABILITY

Amphenol Industrial Operations / Eaxtron contacts are made from pure copper (Cu11 000) and plated with an industry leading 6um of silver. The plating ensures minimal wear and tear on the contact. Even more importantly the patented vortex clip significantly reduces coupling friction, further maximizing the lifetime of the contact.

Polyamide material guarantees robust performance in even the toughest of working conditions. These flexible handles are highly durable, so you can avoid the most common cause and cost of early replacement, broken handles.


By virtue of these innovations, the initial results of ongoing tests show that an AIO connector lasts up to twelve thousand cycles, more than double the industry standard.

SAFETY

Amphenol Industrial Operations' product has Eaxtron designed and patented locking mechanisms that work in conjunction with the user to provide an arcless experience. Additionally the unique design of the female contacts and durable housing nullifies all 'inevitable' arcs. When the connector is load bearing the patented design manages and safely disperses arcs within the connector carriage. All of this innovation allows the user to operate in a truly arcless environment, with none of the risks traditionally posed to both individuals and equipment.

The color coded system prevents non-compatible connection by clearly classifying by color different voltages and applications.

EFFICIENCY



The highly innovative contact loader, allows you to attach wired pilots, auxiliaries, and main contacts faster than ever before, directly to the connector.



Please contact us at **eaxtron@amphenol-aio.com** for more information.

amphenol-industrial.com/eaxtron



Locking collar

Vortex Clip

COLOR CODED CABLE CLAMPS

Identify battery voltages easily thanks to the color coded cable clamps. In addition to the coding pins, AIO's cable clamps allow you to track different battery voltages and types from a distance to avoid any mismatch in use.

Kit of Cable Clamp:

24 V	36 V	48 V	72 V	80 V
Red	Grey	Blue	Green	Black

The cap and bottom cable clamps are the same for males and females, and available for 160A, 320A and 430A connectors.

RELIABLE: PREVENT CABLE DAMAGE

AlO's cable clamps are also self-centering; they will maintain your wires in proper position and preserve the integrity of the cable.

Self-centering cable clamp

ONE LOADER FOR ALL OUR CONTACTS

The clip on contact loader to make wiring the connectors easier. After crimping or soldering contacts to wires, one needs to only clip them (including auxiliaries, air tubes & pilot contacts) to the contact loader to be clipped securely as one in the housing. **Reliable. Safe & Easy.**

Durable

Air tubes or pilot contacts





Everything you need comes ready with instructions for you or your customers to safely install the connectors. No additional adaption is required. Simply install, safely use & reliably trust these patented battery connectors.


LOCKING ADAPTOR

The locking adapter makes the handle interoperable and easily affixed on the Male or Female Connector & DSC Solution.









Please contact us at **eaxtron@amphenol-aio.com** for more information.



Auxillary contacts

© 2022 All Rights Reserved. Amphenol Industrial Operations

amphenol-industrial.com/eaxtron



HOW TO ORDER

Connector (please choose one code per position, below)													
1	2		3 4		5	6							
Connector Kit	Curre	nt Capability	Dability Contact C		На	ndle Length	Handle			Wire Size			
	160	160 A	F	F	Female/ Vortex	S	Short (Female Only	н	Standard (Female Only	1/0	1/0 (50mm²)	Available for 160 and 320	
К	320	320 A						Clip™ Socket	lip™ Socket	- Optional)		- Required)	2/0
(Eaxtron Series)					Mala (Dia	3/0	3/0 (95mm²)						
430	430 A	М	Male/Pin	Male/Pin Left blank for Male/Pin Gender		4/0	4/0 (120mm²)	Available for 320 and 430					

Example: K160M1/0 (Eaxtron Connector Plug Kit; 160A rated; Male Pin; 1/0 Wire Size); K320FSH4/0 (Eaxtron Connector Socket Kit; 320A rated; Female Socket; w/ Short Handle; 4/0 Wire Size); K320FH2/0 (Eaxtron Connector Socket Kit; 320A rated; Female Socket; Standard Handle; 2/0 Wire Size)

Cable Clamp and Accessories						
1	2 3			3		
Cable Clamp	(Color / Voltage) or Clamp Screws Current Capat					
	RD	Red= 24v	160	160 A		
	GY Grey= 36v		320	320A / 430A		
CC (Eaxtron Cable Clamp)	BE Blue= 48v					
	GR					
	BK Black= 80v					
	Screws					
	1000 Standard Cable Clamp Screws (package of 50)					
	2000	Max Cable Screws- 320A connectors (package of 50)				
Examples: CCBK320	(Cable Clar	np: Black 80V: 320 Amps) or CC1000 (Standard Cample	Clamp	Screws)		

0 (Cable Clamp; Black 80V; 320 Amps) or CC1000 (Standard Cample Clamp Screws)

Handles							
	1		2				
	Handle Type	Current Capability					
LHDOR	Long Handle	160	160 A				
LPHDOR	Low Profile Short Orange Handle	320	320A / 430A				
LHM Handle							
Example: LPHDOR160 (Low Profile Short Orange Handle; 160 Amps)							

Contacts					
Part Number	Description				
Main Contacts					
FMC1607	Female Main Contacts 160A, 50mm ² AWG 1/0, (Pk of 2)				
MMC1606	Male Main Contacts 160A, 50mm ² AWG 1/0, (Pk of 2)				
MMC3200	Male Main Contacts 320A, 50mm ² AWG 1/0, (Pk of 2)				
MMC3202	Male Main Contacts 320A, 70mm ² AWG 2/0, (Pk of 2)				
MMC3204	Male Main Contacts 320A, 95mm ² AWG 3/0, (Pk of 2)				
MMC3206	Male Main Contacts 320A, AWG 4/0, (Pk of 2)				
	Auxiliary Pilot & Auxiliary Contacts				
AXP1000	160A Male Auxiliary Pilot & Auxiliary Contacts Kit				
AXP1001	160A Female Auxiliary Pilot & Auxiliary Contacts Kit				
AXP1002	320A Male Auxiliary Pilot & Auxiliary Contacts Kit				
AXP1003	320A Female Auxiliary Pilot & Auxiliary Contacts Kit				

Accessories					
1			2		
Accesory			Current Capability		
CL	Contact Lo	ader	160	160 A	
MH	Male Hous	sing	320	320A / 430A	
FH	Female Ho	using			
CV	Locking Collar				
Example: CL160 (Contact Loader; 160 Amps)					
Double Stack Connector Kits					
Part Number			Description		
DSC	KITP		DSC Plug Kit		
DSC	KITS	DSC Socket Kit			
Coding Keys					
Part N	lumber		Descrip	otion	
CK1	1000		Coding Keys,	(Pk of 12)	

Tools				
Part Number	Description			
OSHA	OSHA Plate			
E2CT1000	Lithium Crimper with Full Set of 6W-Dies			
CCT1000	Hand Crimping Tool with Full Set of 6W-Dies			



Please contact us at **eaxtron@amphenol-aio.com** for more information.

amphenol-industrial.com/eaxtron