5A Heavy Duty Connector Crimp Contacts

multicomp PRO





Specifications

Material : Copper Alloy

Finish : Gold Plated / Silver Plated


Rated Current : 5A Contact Resistance : ≤3mΩ

Wire Diameter Range : 0.09mm² to 0.82mm² (28AWG to 18AWG)


Pluggable Times : ≥500

Diagram

Crimp Contact, Male



Crimp Contact, Female



Part Number				Wire Diameter			
Male		Female		wife Diameter		С	Stripping Length
Gold Plated	Silver Plated	Gold Plated	Silver Plated	mm²	AWG		
MP009640	MP009636	MP009632	MP009628	0.09~0.25	28~24	0.64	
MP009641	MP009637	MP009633	MP009629	0.25~0.33	26~22	0.9	5
MP009642	MP009638	MP009634	MP009630	0.33~0.52	22~20	1.12]
MP009643	MP009639	MP009635	MP009631	0.52~0.82	22~18	1.35	

Dimensions: Millimetres

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



5A Heavy Duty Connector Crimp Contacts



Part Number Table

Description	Part Number
Crimp Contact, Female, 5A, 28-24 AWG, Gold Plated	MP009632
Crimp Contact, Female, 5A, 26-22 AWG, Gold Plated	MP009633
Crimp Contact, Female, 5A, 22-20 AWG, Gold Plated	MP009634
Crimp Contact, Female, 5A, 22-18 AWG, Gold Plated	MP009635
Crimp Contact, Male, 5A, 28-24 AWG, Gold Plated	MP009640
Crimp Contact, Male, 5A, 26-22 AWG, Gold Plated	MP009641
Crimp Contact, Male, 5A, 22-20 AWG, Gold Plated	MP009642
Crimp Contact, Male, 5A, 22-18 AWG, Gold Plated	MP009643
Crimp Contact, Female, 5A, 28-24 AWG, Silver Plated	MP009628
Crimp Contact, Female, 5A, 26-22 AWG, Silver Plated	MP009629
Crimp Contact, Female, 5A, 22-20 AWG, Silver Plated	MP009630
Crimp Contact, Female, 5A, 22-18 AWG, Silver Plated	MP009631
Crimp Contact, Male, 5A, 28-24 AWG, Silver Plated	MP009636
Crimp Contact, Male, 5A, 26-22 AWG, Silver Plated	MP009637
Crimp Contact, Male, 5A, 22-20 AWG, Silver Plated	MP009638
Crimp Contact, Male, 5A, 22-18 AWG, Silver Plated	MP009639

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

