




ANTISTATIC ESD PREMIUM WORK STATION SOLDERING MAT SET WITH WRIST STRAP AND COILED CORD

Order No.: T0051403799

Premium set, comprising a Weller antistatic ESD soldering mat, ESD wrist strap and 2.4 m coiled cord. The soldering mat is heat- and solder-resistant and has an antireflective surface, two 10 mm press studs and rounded corners. The ESD wrist strap is very comfortable to wear, even over long periods, is washable, antibacterial, has high conductivity thanks to the incorporation of silver and carbon in the fabric and guarantees the discharge of electrical charges and the proper processing of sensitive electronic components. The coiled cord is 2.4 m long.

KEY FEATURES

- > SET, COMPRISING SOLDERING MAT AND ANTISTATIC GROUNDING STRAP (WRIST STRAP + 2.4 M COILED CORD)
- > SIZE 600 MM X 900 MM
- > INCL. TWO 10 MM PRESS STUD CONNECTORS
- > HEAT- AND SOLDER-RESISTANT
- > CHEMICAL- AND OIL-RESISTANT
- > PERMANENTLY ELASTIC, ABRASION-RESISTANT AND COMFORTABLE
- > ROHS-COMPLIANT
- > ANTIREFLECTIVE SURFACE MAKES YOUR WORK EASIER
- > DOUBLE-LAYER ESD TABLE MAT (DISSIPATIVE / CONDUCTIVE) 
- > TYPICAL BLEEDER RESISTANCE 10⁶–10⁸ OHMS



**SET, COMPRISING SOLDERING MAT
AND ANTISTATIC GROUNDING STRAP
(WRIST STRAP + 2.4 M COILED CORD)**

LARGE WORK SURFACE

600 mm x 900 mm

**SUITABLE FOR LEFT
& RIGHT HANDS**

Incl. two 10 mm press stud connectors

DURABLE

Permanently elastic, abrasion-resistant
and comfortable

EYE SAFETY

Anti reflective surface
gets the job done faster

BLEEDER RESISTANCE

10⁶ – 10⁸ Ohms



RESISTANT

Heat, solder, chemical and oil-resistant

TESTED



RoHS-compliant




ESD

Double-layer table mat
(dissipative/ conductive)

+ TECHNICAL DATA

ESD SAFE		
WEIGHT IN G / OZ		1600 / 56.438
PRODUCT DIMENSIONS	Wide in mm / in	900 / 35.4331
	Depth in mm / in	600 / 23.622
	Thickness in mm / in	2 / 0.0787
ANTISTATIC ESD WRIST STRAP		
WRIST STRAP & COILED CORD		BGI 818
LENGTH COILED CORD		2.4m



weller-tools.com

Weller® is a registered trademark of Apex Brands, Inc. © 2022 | Specifications subject to change without notice.



Order No.: T0051403799