# 22mm Pilot LED Lamps multicomp PRO



### RoHS **Compliant**

#### **Description**

This superb range of LED lamps offers high illumination output, long life, low temperature and is supplied as a complete unit with encapsulated LED ready to fit. The range provides even lighting in each colour and is available in:

White, amber, red, green and blue

24V AC and DC

110V AC (50 Hz)

230V AC (50 Hz)


#### **Specifications**

: 30.000 hours **Expected Life** 

: IP65 IP Rating **Brightness** : 600 cd / m<sup>2</sup> : -25°C to +55°C **Operating Temperature** 

CE Approved

### **Diagram**



**Dimensions: Millimetres** 

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



# 22mm Pilot LED Lamps multicomp PRO



#### Part Number Table

Description	Part Number
22 mm Switches Led Pilot White 24 V	RAD221B
22 mm Switches Led Pilot White 110 V	RAD221F
22 mm Switches Led Pilot White 230 V	RAD221P
22 mm Switches Led Pilot Green 24 V	RAD223B
22 mm Switches Led Pilot Green 110 V	RAD223F
22 mm Switches Led Pilot Green 230 V	RAD223P
22 mm Switches Led Pilot Red 24 V	RAD224B
22 mm Switches Led Pilot Red 110 V	RAD224F
22 mm Switches Led Pilot Red 230 V	RAD224P
22 mm Switches Led Pilot Amber 24 V	RAD225B
22 mm Switches Led Pilot Amber 110 V	RAD225F
22 mm Switches Led Pilot Amber 230 V	RAD225P
22 mm Switches Led Pilot Test White 24 V	RADT221B
22 mm Switches Led Pilot Test White 110 V	RADT221F
22 mm Switches Led Pilot Test White 230 V	RADT221P
22 mm Switches Led Pilot Test Green 24 V	RADT223B
22 mm Switches Led Pilot Test Green 110 V	RADT223F
22 mm Switches Led Pilot Test Green 230 V	RADT223P
22 mm Switches Led Test Pilot Red 24 V	RADT224B
22 mm Switches Led Pilot Testred 110 V	RADT224F
22 mm Switches Led Pilot Testred 230 V	RADT224P
22 mm Switches Led Pilot Test Amber 24 V	RADT225B
22 mm Switches Led Pilot Test Amber 110 V	RADT225F
22 mm Switches Led Pilot Test Amber 230 V	RADT225P

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

