

# Safe-Torque A 1 Set 1, 1/4" square head drive, 2-12 Nm, 10 pieces


## Safe-Torque torque wrenches



<b>EAN:</b>	4013288223005	<b>Size:</b>	275x140x65 mm
<b>Part number:</b>	05075830001	<b>Weight:</b>	1023 g
<b>Article number:</b>	Safe-Torque A 1 Set 1	<b>Country of origin:</b>	CZ
		<b>Customs tariff number:</b>	82079030

- Slip-over release mechanism - the set torque can never be overtightened
- Torque Lock function: The torque function can be deactivated and the tool can then be used as a standard ratchet with high loosening moments and for applications with defined angles of rotation
- For controlled clockwise and counterclockwise torque operation - tightening and loosening with or without torque
- Easy setting and saving of the desired torque value with audible and tactile clicks when reaching the scale values
- After the target torque has been reached, the release angle is only 30°
- The fine toothing with 72 teeth allows for a low return angle of 5°
- 1/4" square head drive with socket locking

10-piece 1/4" torque wrench set in a robust textile box; torque wrench with slide-over mechanism. Once the set torque has been reached, the tool cannot be overtightened, so that excessive torque cannot be applied. Setting range of 2 to 12 Nm for controlled clockwise and counterclockwise torque operation. Easy setting and saving of the default value: The audible and tactile clicks on reaching the scale values facilitate the safe setting of the desired torque value. The Torque Lock function allows use as a standard ratchet without torque function. Thus also usable for applications with angles of rotation. Max. breaking torque of the 1/4" square head as per DIN 3122. The return angle of only 5° allows the ratchet to be used even in confined spaces. Included are: Safe-Torque A 1 torque wrench, 1/4" square head, 2-12 Nm, 8 sockets with 1/4" drive and one short extension.



### Web link

[https://products.wera.de/en/torque\\_tools\\_safe-torque\\_torque\\_wrenches\\_and\\_accessories\\_safe-torque\\_torque\\_wrenches\\_safe-torque\\_a\\_1\\_set\\_1.html](https://products.wera.de/en/torque_tools_safe-torque_torque_wrenches_and_accessories_safe-torque_torque_wrenches_safe-torque_a_1_set_1.html)

Wera - Safe-Torque A 1 Set 1  
05075830001 - 4013288223005

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: info@wera.de

Safe-Torque torque wrenches

Slide-over mechanism prevents application of excessive torques



Safe-Torque




The Safe-Torque A 1 torque wrench is equipped with a slide-over mechanism. Once the set torque value has been reached, the tool cannot be overtightened, so that excessive torque cannot be applied.

Torque Lock function



The torque function can be deactivated. The Safe-Torque torque wrench can then also be used as a standard ratchet with high loosening moments and for applications with defined angles of rotation.

For clockwise and counterclockwise operation




The Safe-Torque torque wrench is suitable for clockwise and counterclockwise operation with a set torque. When the Torque Lock function is deactivated, tightening and loosening is enabled without torque.

Easy torque setting



Easy setting and saving of the required torque with audible and tactile clicks on reaching the scale values.

Low return angle



The fine-toothed Safe-Torque torque wrench with 72 teeth has a back-pivoting angle of only 5°. The small stroke offers quick and precise working in all installation positions.

For 1/4" sockets



The Safe-Torque A 1 torque wrench has 1/4" square head mounting and is suitable for 1/4" sockets.

Space for more tools



The Wera Belts can be attached to the hook and loop fastener strips in the textile box of the sets Safe-Torque A 1 Set 1 and Safe-Torque A 1 Imperial Set 1, so more sockets and/or bit sockets can be stored and transported.

Web link

[https://products.wera.de/en/torque\\_tools\\_safe-torque\\_torque\\_wrenches\\_and\\_accessories\\_safe-torque\\_torque\\_wrenches\\_safe-torque\\_a\\_1\\_set\\_1.html](https://products.wera.de/en/torque_tools_safe-torque_torque_wrenches_and_accessories_safe-torque_torque_wrenches_safe-torque_a_1_set_1.html)

Wera - Safe-Torque A 1 Set 1  
05075830001 - 4013288223005

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)

## Safe-Torque A 1 Set 1, 1/4" square head drive, 2-12 Nm, 10 pieces



### Safe-Torque torque wrenches

#### Set contents:

#### Safe-Torque A 1 torque wrench with 1/4" square head drive, 2-12 Nm, 1/4" x 2-12 Nm

05075800001 1x 1/4" x 2-12 Nm



#### 8790 HMA Zyklus 1/4" socket, 5.5 x 23 mm



05003504001	1x	5.5 x 23 mm
05003505001	1x	6 x 23 mm
05003506001	1x	7 x 23 mm
05003507001	1x	8 x 23 mm
05003509001	1x	10 x 23 mm
05003510001	1x	11 x 23 mm
05003511001	1x	12 x 23 mm
05003512001	1x	13 x 23 mm

#### 8794 SA Zyklus extension with free-turning sleeve, short, 1/4", 1/4" x 75 mm



05003525001 1x 1/4" x 75 mm

#### Hook and Loop Fastener Strip 240, 50 x 240 mm

1x 50 x 240 mm



#### Web link

[https://products.wera.de/en/torque\\_tools\\_safe-torque\\_torque\\_wrenches\\_and\\_accessories\\_safe-torque\\_torque\\_wrenches\\_safe-torque\\_a\\_1\\_set\\_1.html](https://products.wera.de/en/torque_tools_safe-torque_torque_wrenches_and_accessories_safe-torque_torque_wrenches_safe-torque_a_1_set_1.html)

Wera - Safe-Torque A 1 Set 1  
05075830001 - 4013288223005

Wera Werkzeuge GmbH  
Korzter Straße 21-25  
D-42349 Wuppertal  
Tel: +49 (0)2 02 / 40 45-0  
E-Mail: [info@wera.de](mailto:info@wera.de)