

3 m (9.8 ft.) HDMI to DisplayPort Cable - 4K 30Hz

**Product ID:** HD2DPMM3M



This 3 m (10ft.) HDMI to DisplayPort cable with USB power lets you connect an HDMI video source, such as your laptop, desktop, Blu-ray player, or camera, to a DisplayPort monitor or projector without the need for additional video cables. The adapter cable features male connectors enabling you to connect your video source directly to the display, with no need for additional adapters or cables.

The active HDMI 1.4 to DisplayPort 1.2 converter cable offers plug-and-play installation, providing a hassle-free setup with no software or drivers to install. The adapter is powered via a USB port, avoiding the need for an extra power adapter.

With support for 4K at 30Hz, you get a sharp, crisp picture that's richer and more true-to-life than traditional HD, with far greater detail. The HDMI to DisplayPort Adapter cable delivers Ultra HD content to your DisplayPort monitor and supports 7.1 channel surround sound audio.

The HDMI to DisplayPort adapter is backward compatible with 1080p and 1440p displays, which makes it a great accessory to future-proof your existing setup for 4K video.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

The HD2DPMM3M is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

- Use in your boardroom or office workstations for installations requiring 3 meters (9.8 feet) of cable
- Connect your HDMI computer to a DisplayPort monitor
- Viewing video footage from your HDMI source on a DisplayPort monitor

## Features

- Provides a convenient plug-and-play solution with no additional cables required
- Active HDMI to DisplayPort conversion transmits high-definition audio and video from your computer to a DP monitor
- Deliver astonishing picture quality with support for video resolutions up to Ultra HD 4K

---

### Hardware

Warranty	2 Years
Active or Passive Adapter	Active
AV Input	HDMI - 1.4
AV Output	DisplayPort
Audio	Yes
Chipset ID	MegaChips Technology - STDP2600

---

### Performance

Video Revision	HDMI 1.4
Maximum Digital Resolutions	3840 x2160
Supported Resolutions	DisplayPort: 3840x2160 (4K) / 30Hz Additional resolutions and refresh rates may be supported
Wide Screen Supported	Yes
Audio Specifications	DisplayPort - 7.1 Channel Audio

---

### Connector(s)

Connector A	1 - HDMI (19 pin)
-------------	-------------------



Connector B	1 - DisplayPort (20 pin)
-------------	--------------------------

---

**Power**

Power Source	USB-Powered
--------------	-------------

---

**Environmental**

Operating Temperature	0C to 70C (32F to 158F)
-----------------------	-------------------------

Storage Temperature	-10C to 55C (14F to 131F)
---------------------	---------------------------

Humidity	5~90% RH (Non-condensing)
----------	---------------------------

---

**Physical Characteristics**

Color	Black
-------	-------

Material	Plastic
----------	---------

Product Length	9.8 ft [3.0 m]
----------------	----------------

Product Width	0.8 in [2.1 cm]
---------------	-----------------

Product Height	0.4 in [1.1 cm]
----------------	-----------------

Weight of Product	7.1 oz [200.0 g]
-------------------	------------------

---

**Packaging Information**

Package Quantity	1
------------------	---

Package Length	7.9 in [20.0 cm]
----------------	------------------

Package Width	8.6 in [21.8 cm]
---------------	------------------

Package Height	1.0 in [2.5 cm]
----------------	-----------------

Shipping (Package) Weight	7.2 oz [205.0 g]
---------------------------	------------------

---

**What's in the Box**

Included in Package	1 - HDMI to DisplayPort Cable
---------------------	-------------------------------

---

***\*Product appearance and specifications are subject to change without notice.***

