

1m USB A to USB C Charging Cable - Durable Fast Charge & Sync USB 2.0 to USB Type C Data Cord - Rugged TPE Jacket Aramid Fiber M/M 3A White - Samsung S10, iPad Pro, Pixel

Product ID: RUSB2AC1MW



This USB C cable withstands the daily demands of charging and syncing your mobile devices. Compatible with your Thunderbolt 3 ports, this rugged cable is a must-have for both business and consumer applications.

The durable USB C charging cable has aramid fiber reinforcement that shelters it from the stress of frequent bends. This also lets the cable flex without over-stretching or damaging the core of the cable.

- Aramid fiber adds strength and durability to the cable
- Insulated conductors reduce friction, provide more flexibility
- EMI (electromagnetic interference) protection with aluminum-mylar foil with braided shielding
- TPE (thermoplastic elastomer) cable jacket is more flexible than a standard PVC cable

The USB A to USB C cable is constructed to prevent the connector from separating from the jacket. The extra-long strain relief molding is tested to withstand over 10,000+ bend cycles at a 180 angle.

<0|>

- USB Type C connector provides 3A of power output for charging your USB C compatible devices
- Metal shield protects circuit board from EMI and reinforces the connection point
- Strain relief tested to tolerate over 10,000+ bend cycles at a 180 angle

The durable cable supports all USB 2.0 specifications providing a dependable connection for all your USB-C devices. It also delivers up to 60W of power to charge your devices without needing an additional power supply.

RUSB2CC1MW is backed by a StarTech.com lifetime warranty and free lifetime technical support.



## **Certifications, Reports and Compatibility**



## Applications

• Charge and sync your USB Type C mobile devices

## Features

• DURABLE: USB A to USB C charging cable reinforced w/ aramid fiber for increased tensile strength 5x stronger than steel. Tested to withstand 10000+ bend cycles at 180 angle & 5000+ insertions

• SPECS: Length: 1m (3ft) Color: White Connectors: USB-C to USB-A Performance: USB 2.0 Material: Aramid Fiber Power: 3A Jacket Type: TPE Shielding: EMI Protection

• USB-C COMPATIBILITY: Rugged data transfer cable allows you to charge and sync your USB Type C devices including your iPad Pro, Samsung Galaxy S8, S9, S10, S20, S20+, One Plus & Google Pixel 3a, 3, 4 series

• FAST CHARGE AND SYNC : Supporting up to 3A for fast charging from a USB-A port or Quick Charge power adapter, this high quality cord is designed to charge and sync your USB C devices

• FLEXIBLE CABLE: Built with a TPE jacket to absorb the stress of frequent bends without damaging the core of the cable. TPE is non-toxic, halogen free & RoHS certified for environmental sustainability

Hardware		
	Warranty	Lifetime
	Connector Plating	Nickel
	Cable Jacket Material	TPE - Thermoplastic Elastomers
	Cable Shield Material	Aluminum-Mylar Foil with Braid
Performance		
	Type and Rate	USB 2.0 - 480 Mbit/s
Connector(s)		
	Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
	Connector B	1 - USB Type-C (24-pin) USB 2.0 (480Mbps)



## Physical Characteristics

	Color	White
	Connector Style	Straight
	Wire Gauge	22/32 AWG
	Cable Length	3.3 ft [1 m]
	Product Length	39.4 in [100.0 cm]
	Product Width	0.6 in [1.4 cm]
	Product Height	0.3 in [7 mm]
	Weight of Product	0.9 oz [25 g]
Packaging Information		
	Package Quantity	1
	Package Quantity Package Length	1 8.7 in [22 cm]
	Package Length	8.7 in [22 cm]
	Package Length Package Width	8.7 in [22 cm] 4.9 in [12.5 cm]

\*Product appearance and specifications are subject to change without notice.