
Push Pull Connector Plastic IP50

multicomp PRO


RoHS Compliant




Diagram



NOTE; BEND RELIEF MUST BE ORDERED SEPARATELY





Dimensions: Millimetres

Specifications

Material

Housing (Body) : PC Insulator : PPS

Terminal : Brass, Gold Plated

Electrical

Voltage Rating : 250V
Current Rating : See chart
Dielectric withstanding voltage : See chart
Electrical Life : 1,000 Cycles min.

Temperature Rating

Operating temperature : -55°C to +118°C

Environmental

IP50 Protection (Mated Condition)

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro




Push Pull Connector Plastic IP50

multicomp PRO

	2 Pin	3 Pin	4 Pin	5 Pin	6 Pin	7 Pin	8 Pin	9 Pin	10 Pin	14 Pin
Configuration										
Diameter of Pin	1.3	1.3	0.9	0.9	0.7	0.7	0.7	0.5	0.5	0.5
Testing Voltage	1200V	1200V	1200V	1200V	1000V	1000V	1000V	800V	800V	800V
Working Voltage	300V	300V	250V	250V	200V	200V	200V	200V	200V	200V
Rated Current / Pin	20A	12A	10A	9A	8A	7A	6A	4A	4A	4A

Allignment Key Option						
Q°	\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\\	66,7	80'			
Key G	Key A	Key B	Key C			



Part Number Table

Description	Position	Part Number
	2	MCP-P1PG02SG52B
	3	MCP-P1PG03SG52B
	4	MCP-P1PG04SG52B
Mala Cannactar plus Amm to F 2mm Bond Baliaf Cray	5	MCP-P1PG05SG52B
Male Connector plug, 4mm to 5.2mm, Bend Relief, Gray	6	MCP-P1PG06SG52B
	7	MCP-P1PG07SG52B
	8	MCP-P1PG08SG52B
	10	MCP-P1PG10SG52B

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

