



Note: This datasheet may be out of date. Please download the latest datasheet of GCQ1555C1H6R8WB01# from the official website of Murata Manufacturing Co., Ltd.

"#" indicates a package specification code.

http://www.murata.com/en-gb/products/productdetail?partno=GCQ1555C1H6R8WB01%23

# GCQ1555C1H6R8WB01D

















< List of part numbers with package codes > GCQ1555C1H6R8WB01D GCQ1555C1H6R8WB01W

### GCQ1555C1H6R8WB01J



## Appearance & Shape







### References

Packaging	Specifications	Standard Packing Quantity
D	180mm Paper Tape	10000
W	180mm Paper Tape (W8P1)	20000
J	330mm Paper Tape	50000

Mass (typ.)		
1 piece	1.6mg	
φ180mm Reel	118g	

1 of 2

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



GCQ1555C1H6R8WB01D



Note: This datasheet may be out of date.  $Please\ download\ the\ latest\ data sheet\ of\ GCQ1555C1H6R8WB01\#\ from\ the\ official\ website\ of\ Murata$ Manufacturing Co., Ltd.

http://www.murata.com/en-gb/products/productdetail?partno=GCQ1555C1H6R8WB01%23

"#" indicates a package specification code.



# **Specifications**

Length	1.0±0.05mm
Width	0.5±0.05mm
Thickness	0.5±0.05mm
Capacitance	6.8pF ±0.05pF
Distance between external terminals g	0.3mm min.
External terminal size e	0.15 to 0.35mm
Operating Temperature Range	-55°C to 125°C
Rated Voltage	50Vdc
Size code in inch(mm)	0402 (1005M)
тс	0±30ppm/°C
Temperature characteristics (complied standard)	C0G(EIA)
Temperature range of temperature characteristics	25°C to 125°C

2 of 2

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

