# Push Pull Connector IP68 Metal


## multicomp PRO


#### RoHS Compliant



#### Diagram







Panel Cut—Out (Rear Panel Mounting)

#### **Specifications**

Material Dimensions : Millimetres

Housing (Body) : Brass, Natural Chrome plated Insulator : PPS, Colour Beige

Terminal : Brass, Gold Plated

**Electrical** 

Voltage Rating : 250V
Current Rating : See chart
Dielectric withstanding voltage : See chart
Electrical Life : 1,000 Cycles min.

Mechanical

Endurance : 5,000 Cycles min.

**Temperature Rating** 

Operating temperature : -55°C to +150°C

**Environmental** 

IP68 Protection (Mated Condition)


Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro





### **Push Pull Connector IP68 Metal**


### multicomp PRO


	2 Pin	3 Pin	4 Pin	5 Pin	6 Pin	7 Pin	12 Pin
Configuration							
Diameter of Pin	Ø1.3	Ø1.3	Ø0.9	Ø0.9	Ø0.7	Ø0.7	Ø0.5
Testing Voltage	1200V	1200V	1150V	1100V	1000V	1000V	800V
Working Voltage	350V	350V	300V	300V	250V	250V	200V
Rated Current / Pin	12A	11A	8A	7A	5A	5A	3A























#### **Part Number Table**

Description	Position	Part Number
	2	MCP-M1RS102P-IP68
	3	MCP-M1RS103P-IP68
Duch Dull Cooket ID60	4	MCP-M1RS104P-IP68
Push Pull Socket, IP68	5	MCP-M1RS105P-IP68
	6	MCP-M1RS106P-IP68
	7	MCP-M1RS107P-IP68

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

