

SMX-200X-XX

41-pin, Unterminated Cable Assembly - Part No: 70-0363-506R (pigtail), 3 ft. The mating cable assembly (length = 3ft, teflon cable, 16GA) with one end unterminted for SMX-200X-XX cards.



Connector Kit - Part No: 70-0190-001R

(includes 1 connector housing, 44 crimp pins, 1 strain relief bracket etc). For making a customized length cable, customer needs to buy the kit along with the tools, (cables not included).



SMX-200X-XX Crimp, Insert and Extraction Tools

Crimp Tool and Turret Head - Part No: 46-0012-000 Mfg. part no: 9501 and 9502-1 - Manufacturer: Positronics



Insertion Tool - Part No: 46-0014-000

Mfg. part no: 9099 – Manufacturer: Positronics



Extraction Tool - Part No: 46-0015-000

Mfg. part no: 9081 - Manufacturer: Positronics



SMX-200X-XX Additional Parts

Contact/Female/Crimp Pwr/14-16 GA - Part No: 27-0087-000 Mfg. part no: FC114N2/AA - Manufacturer : Amphenol Positronic



Strain Relief Bracket Kit - Part No: 41-0513-000R

For 41-pin series m conn







SMX-300X

Part No: 70-0367-207R

(F/A, SMX-300X-TB160-3, 160-160P #3) (Break Out Box) 160-pin BOB_SMX-300X



SMX-32XX

Part No: 70-0367-206R

(F/A, SMX-327X TB160-1, 160-160P #1) (Break Out Box) 160-pin BOB SMX-327X



SMX-44XX

Part No: 70-0367-208R

(F/A,SMX 44XX-TB160-4,160-160P #4) (Break Out Box) 160-pin BOB_SMX-44XX



SMX-5001 & SMX-5002

Part No: 70-0367-205R

(F/A, SMX, TB160SE, 160-160P) (Break Out Box) 160-pin BOB_SMX-500X



SMX-5004

50 Pin Connector kit - Part No: 52-0195-000

(Includes two 50-pin connector, two Backshells and 104 Crimp pins)



Crimp Tool - Part No: 46-0024-000

Mfg. part no: 9507, Manufacturer: Positronic



Insertion Tool - Part No: 46-0037-000

Mfg. part no: 9099-1, Manufacturer: Positronic



Extraction Tool - Part No: 46-0036-000

Mfg. part no: 9081-1, Manufacturer: Positronic



PositronicTurret Head Position Tool - Part No: 46-0025-000

Mfg. part no: 9502-12, Manufacturer: Positronic





160-PIN CONNECTOR (Unterminated)

160-pin, Unterminated Cable Assembly – **Part No: 70-0363-552R** (pigtail), 3 ft.



Crimp tool - Part No: 46-0010-000

Mfg. part no: 014374 - Manufacturer: Ernie



Extraction Tool - Part No: 46-0011-000

Mfg. part no: 471555 - Manufacturer: Ernie



STRAIN RELIEF BRACKET KIT (Without Connector)

KIT, Strain Relief - Part No: 70-0409-160R for 160-pin DIN Connector



CRIMP PIN

Crimp Pins - Part No: 52-0109-000R for 160-pin DIN Connector (pack of 100)

Crimp Pins - Part No: 52-0109-001R for 160-pin DIN connector (Reel of 500 Pins)



MATING CONNECTOR

Connector Housing - Part No: 27-0088-160

160-pin female, Euro-DIN





SMX-61XX-PkZ

- 1. Customer has to select either one of the below mentioned PkZ Housing.
- 2. Based on the selected housing, customer has to select the relevent cables mentioned below.
- 3. Select the number of cables as per the channel required.

PkZ Housing - Part No: 27-0970-000

PKZ Connector Housing for cables Ø.040-Ø.054 Housing, 53 position, PkZ plug, w/ 2 strain relief, for cables Ø.040-Ø.054 Manufacturer/Part Number: PHOENIX / PRC532DX1XANONE




PkZ Housing - Part No: 27-0970-001

PkZ Connector Housing for cables Ø.061-Ø.102 Housing, 53 position, PkZ plug, w/ 2 strain relief, for cables Ø.061-Ø.102 Manufacturer/Part Number: PHOENIX PRC532DX2XANONE



PkZ to SMB, 1.37mm Cables - Part No: 56-0900-002

PkZ to SMB, 1.37mm Cable Assembly (24" Long) Cable Assy, PkZ plug to SMB plug,1.37mm cable, 24 Inch Manufacturer/Part Number PHOENIX 15609DY0003-240




PkZ to SMB, RG178 Cables - Part No: 56-0901-002

PkZ to SMB, RG178 Cable Assembly (24" Long) Cable Assy, PkZ plug to SMB plug, RG178 cable, 24 Inch Manufacturer/Part Number PHOENIX 15609230092-240



PkZ to SMA, 1.37mm Cables - Part No: 56-0902-002

PkZ to SMA, 1.37mm Cable Assembly (24" Long) Cable Assy, PkZ plug to SMA plug, 1.37mm cable, 24 Inch Manufacturer/Part Number PHOENIX 15620DY0004-240



PkZ to SMA, RG178 Cables - Part No: 56-0903-002

PkZ to SMA, RG178 Cable Assembly (24" Long) Cable Assy, PkZ plug to SMA plug, RG178 cable, 24 Inch Manufacturer/Part Number PHOENIX 15620230076-240

