

# Ratchet wrenches

## 67 Ratchet combination wrenches

▷ ISO 1711-1.

- Reversible ratchet system incorporated within a compact ring head.
- High performance, suitable for aircraft fasteners.
- Integral reversing lever avoids any risk of accidental reversal.
- Wrench angled at 15°.
- 5° increments (6° for sizes 8 and 9).
- Satin chrome finish.

Size	B mm	D mm	B' mm	C mm	C' mm	L mm	H mm	ΔΔ g
67.6	15	7,5	14	4	6,3	128	2,8	27
67.7	16,7	7,5	17	4,3	6,5	140	2,8	32
67.8	16,7	7,5	17	4,3	6,5	140	2,8	42
67.9	18,7	8	18,6	4,5	6,9	149	3	50
67.10	20,8	8,8	20,2	5	7,3	158	3,4	59
67.11	23	9,9	22	5,3	7,7	165	3,7	71
67.12	24,6	10,8	23,4	5,5	8,2	171	4	88
67.13	26,8	11,8	25,5	6,1	8,6	178	4,3	101
67.14	29	12,6	26,9	6,5	9	190	4,5	119
67.15	31	13,4	28,3	6,8	9,4	199	4,7	138
67.16	33	14,1	29,8	7,1	9,9	208	4,9	153
67.17	35,5	15,2	31,8	7,5	10,3	225	5,3	186
67.18	37,5	16,1	32,7	8,1	10,7	236	5,5	211
67.19	39,4	16,8	34	8,6	11,2	247	5,7	243
67.21	45,8	19,5	40,1	9	13	287,8	6,3	343
67.22	45,8	19,5	40,1	9	13	287,8	6,3	343
67.24	51,8	22,1	46,5	10	14,5	321	6,5	476
67.27	56,4	25	52,4	10,8	15,5	356,6	8,4	693
67.30	62,7	27	58,1	11,5	17	400,7	8,5	891
67.32	66,4	29,2	61,9	12,4	17,5	423,5	9,5	1079



## 67 Metric ratchet combination wrench sets

• Supplied as rack, module or box sets.

Size	Module	Part No.	Range mm	Weight kg
67.JP9			8-10-11-12-13-16-17-18-19	1,195
67.J7	•		8-10-12-13-14-17-19	0,876
MOD.67J12		PL.652	8-9-10-11-12-13-14-15-16-17-18-19	1,590
MOD.67XL		PL.653	21-22-24-27-30-32	4,090



## ▶ Short ratchet combination wrench series


**67S**

## Short reversible ratchet combination wrenches

### ACCESSIBILITY FIRST

*Easier servicing and repair.*

- Ideal for applications that present problems in terms of :
  - congestion,
  - visibility and accessibility.
- Saves time.
- Comfortable to use.
- Automotive applications : working around the engine block or gearbox, instrument panel, steering column, electric or control panels.



### Unbeatably ultra-compact.

- 40% more compact than a traditional ratchet combination wrench.

*Ideal for applications where access is limited.*

