



Nylon 6.6 Machine Screw Insulators						
Product Code	Size	Length	A	B	C	D
164002003	M2	3.0	4.2	1.0	3.0	2.1
164002004	M2	4.0	4.2	1.0	3.0	2.1
164003002	M3	2.0	6.2	1.0	4.0	3.1
164003003	M3	3.0	6.2	1.0	4.0	3.1
164003004	M3	4.0	6.2	1.0	4.0	3.1
164003005	M3	5.0	6.2	1.0	4.0	3.1
164003006	M3	6.0	6.2	1.0	4.0	3.1
164003007	M3	7.0	6.2	1.0	4.0	3.1
164003008	M3	8.0	6.2	1.0	4.0	3.1
164003009	M3	9.0	6.2	1.0	4.0	3.1
164003010	M3	10.0	6.2	1.0	4.0	3.1
164004003	M4	3.0	8.2	1.5	6.0	4.1
164004004	M4	4.0	8.2	1.5	6.0	4.1
164004005	M4	5.0	8.2	1.5	6.0	4.1
164004007	M4	7.0	8.2	1.5	6.0	4.1
164004009	M4	9.0	8.2	1.5	6.0	4.1
164004012	M4	12.0	8.2	1.5	6.0	4.1
164005003	M5	3.0	10.2	2.0	7.0	5.1
164005004	M5	4.0	10.2	2.0	7.0	5.1
164005005	M5	5.0	10.5	2.0	7.0	5.1
164005007	M5	7.0	10.2	2.0	7.0	5.1
164005009	M5	9.0	10.2	2.0	7.0	5.1
164006004	M6	4.0	12.2	2.0	8.0	6.1
164006006	M6	6.0	12.2	2.0	8.0	6.1
164006008	M6	8.0	12.2	2.0	8.0	6.1
164006010	M6	10.0	12.2	2.0	8.0	6.1
164006012	M6	12.0	12.2	2.0	8.0	6.1
164008004	M8	4.0	14.2	2.5	10.0	8.1
164008006	M8	6.0	14.2	2.5	10.0	8.1
164008008	M8	8.0	14.2	2.5	10.0	8.1
164008010	M8	10.0	14.2	2.5	10.0	8.1
164008012	M8	12.0	14.2	2.5	10.0	8.1
164010006	M10	6.0	30.0	1.5	11.2	10.5
164010010	M10	10.0	30.0	1.5	11.2	10.5
164010012	M10	12.0	30.0	1.5	11.2	10.5
164010015	M10	15.0	30.0	1.5	11.2	10.5
164010023	M10	23.0	30.0	1.5	11.2	10.5
164012016	M12	16.0	30.0	2.0	16.0	13.0
164020017	M20	17.5	36.0	2.0	22.0	20.2

The above sizes are to tolerance plus/minus 0.13mm.

Nylon screw insulators are used to isolate Metal Screws. They are excellent electrical insulators, resist corrosion and can be used as light load bearings.