



Main

Range	TeSys
Device short name	LA9G
Product or Component Type	Set of connections
Accessory / separate part category	Connection accessory
Electrical circuit type	Reversing
Quantity per Set	Set of 1

Complementary

Poles description	3P
Product Compatibility	LC1G115...225 LC1G205...245
Range compatibility	TeSys G
Height	1.77 in (45 mm)
Width	2.44 in (62.1 mm)
Depth	9.16 in (232.6 mm)
Net Weight	2.20 lb(US) (1.0 kg)

Environment

Standards	EN/IEC 60947-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 GB/T 14048.4
Product certifications	ABS BV CB CCC CCS CUL CE DNV-GL EAC KC LROS (Lloyds register of shipping) RCM RINA RMRoS
Ambient air temperature for operation	-40...140 °F (-40...60 °C)
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)
IP degree of protection	IP20 IEC 60529
Operating altitude	9842.52 ft (3000 m) without derating 5000 m with derating factor

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	22328-TESYS GIGA ACCESSORIES
Discount Schedule	112
GTIN	3606481916686
Nbr. of units in pkg.	1
Package weight(Lbs)	2.60 lb(US) (1.18 kg)
Returnability	No

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	3.74 in (9.5 cm)
Package 1 width	4.33 in (11.0 cm)
Package 1 Length	15.55 in (39.5 cm)
Unit Type of Package 2	S04
Number of Units in Package 2	9
Package 2 Weight	25.81 lb(US) (11.706 kg)
Package 2 Height	11.81 in (30.0 cm)
Package 2 width	15.75 in (40.0 cm)
Package 2 Length	23.62 in (60.0 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes
Halogen content performance	Halogen free plastic parts product