



### Main

Range	TeSys
Device short name	LA9G
Product or Component Type	Mechanical interlock
Accessory / separate part category	Interlocking accessory
Interlocking type	Mechanical
Range Compatibility	TeSys Giga
Product Compatibility	LC1G115...500 LC1G205...475
Poles description	3P 4P
Electrical circuit type	Reversing Star-delta Changeover

### Complementary

Height	1.97 in (50 mm)
Width	3.15 in (80 mm)
Depth	4.72 in (120 mm)
Net Weight	0.55 lb(US) (0.25 kg)

### Environment

Pollution degree	3 IEC 60947-1
IP degree of protection	IP20 conforming to IEC 60529
Operating altitude	9842.52 ft (3000 m) without derating 5000 m with derating factor
Ambient Air Temperature for Operation	-13...140 °F (-25...60 °C)
Ambient Air Temperature for Storage	-76...176 °F (-60...80 °C)
Standards	EN/IEC 60947-4-1 UL 60947-4-1 CSA C22.2 No 60947-4-1 GB/T 14048.4

### Ordering and shipping details

Category	22328-TESYS GIGA ACCESSORIES
Discount Schedule	I12
GTIN	00785901996798
Returnability	Yes
Country of origin	CN

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	2.17 in (5.5 cm)
Package 1 Width	3.35 in (8.5 cm)
Package 1 Length	7.20 in (18.3 cm)
Package 1 Weight	6.70 oz (190.0 g)
Unit Type of Package 2	S02

Number of Units in Package 2	12
Package 2 Height	5.91 in (15.0 cm)
Package 2 Width	11.81 in (30.0 cm)
Package 2 Length	15.75 in (40.0 cm)
Package 2 Weight	5.82 lb(US) (2.64 kg)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Styrene, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
PVC free	Yes
Halogen content performance	Halogen free plastic parts product