

APM IoT Gateway

For remote monitoring of APMs using the Trumeter Cloud



An all in one remote monitoring solution for APMs and designed for easy integration, the **IoT Gateway** with **Trumeter Cloud** provides a powerful feature set in a cost effective package.

For use with the entire APM range, the IoT Gateway instantly gives you the ability to remotely monitor readings and status of your systems, as well as alarm alerts via email and SMS. With the ability to interface with up to 4 meters, the IoT Gateway is plug and play out of the box and includes free access to the **Trumeter Cloud** online dashboard.

Otrumet

CELLULAR IOT GATEWAY








Trumeter Cloud Pricing Plans

Anyone with an IoT Gateway or Vista Touch automatically has **FREE** access to the **Standard** plan, but you'll likely want to upgrade to one of our other plans to take advantage of monitoring multiple devices with increased data storage and communication capabilities. Choose your plan at www.trumeter.com/cloud/plans



*Ethernet Device includes IoT Gateway or ethernet enabled APM or Vista Touch. Additional Ethernet Devices: \$3 / month. Additional Cellular Gateways: \$5 / month.


Go to www.trumeter.com for further information





Power Supply		Network	
Voltage Current	9-36V 60mA(aver) @9VDC	Cellular Ethernet	UK/EU 4G (supplied with antenna) 10/100 Ethernet RJ45
Current	30mA(aver) @36VDC	Luemer	
AC Power Supply	100-240V AC, 50/60Hz		
EMC			
ESD	IEC61000-4-2, Level 2		
Surge	IEC61000-4-5, Level 3		
Fast Transient	IEC61000-4-4, Level 3		
Radiated Immunity	IEC61000-4-3		
Conducted Immunity	IEC61000-4-6		
Digital Inputs		Analog Inputs	
Number of Interfaces	4 Digital Inputs	Number of Interfaces	4 Analog Inputs
Voltage Range	0-50VDC	Input Range	0-20mA DC
Voltage High	>2VDC		
Voltage Low	<2VDC		

Dimensions





Part Numbers

IOT-GATEWAY-4G IOT-GATEWAY-ETH IOT-GATEWAY-XXX

IoT Gateway with 4G (UK/Europe) for APM with Trumeter Cloud online dashboard access IoT Gateway with Ethernet connection for APM Trumeter Cloud online dashboard access **Custom Option**



www.trumeter.com

Trumeter (The Americas) 6601 Lyons Rd, Suite H-7

Coconut Creek, Florida FL 33073, Tel: +1 954 725 6699 Email: sales.usa@trumeter.com

Trumeter (Europe) Pilot Mill Alfred Street Bury, BL9 9JR Tel: +44 161 674 0960 Email: sales.uk@trumeter.com

Innovative Design Technologies Sdn. Bhd Lot 5881, Lorong Iks Bukit Minyak 1

Taman Perindustrian Iks, 14000 Bukit Tengah Penang, Malaysia Web: www.idtworld.com Tel: + 604 5015700 Email: sales.my@idtworld.com