

**Description**: MHF4 - SMA Female Jumper Cable

Series: Cable Assembly

PART NUMBER:W9017BDXXXX



### Features:

- Low Loss mini coax cable
- OD 0.81mm
- Color Black
- Various cable lengths available, refer to page 2.
- RoHS compliant

## **Applications:**

- SMA Female to MHF-4 jumper cable
- RF connections for radios and antennas
- Connection from radio to external antennas

All dimensions are in mm / inches

#### Issue: 1901

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden. For more information:

Pulse Worldwide Headquarters 15255 Innovation Drive #100 San Diego, CA 92128 USA Tel:1-858-674-8100 Pulse/Larsen Antennas 18110 SE 34<sup>th</sup> St Bldg 2 Suite 250 Vancouver, WA 98683 USA Tel: 1-360-944-7551 Europe Headquarters Pulse GmbH & Do, KG Zeppelinstrasse 15 Herrenberg, Germany Tel: 49 7032 7806 0 Pulse (Suzhou) Wireless Products Co, Inc. 99 Huo Ju Road(#29 Bldg,4<sup>th</sup> Phase Suzhou New District Jiangsu Province, Suzhou 215009 PR China Tel: 86 512 6807 9998



1



**Description:** MHF4 - SMA Female Jumper Cable

Series: Cable Assembly

### PART NUMBER:W9017BDXXXX

	ELECTRICAL	SPECIFICATIONS			
Frequency		0~7.1GHz			
Nominal Impedance		50±2 Ω			
RL of Port-SMA Fer	-10dB(Max)				
RL of Port-MHF4		-10dB(Max)			
Max operating volta	ige(V)	1000			
	Overall Attenuation/dB				
Frequency	W9017BD0100	W9017BD0200	W9017BD0250		
0.1MHz	0.04	0.06	0.07		
1G	0.47	0.77	0.90		
2G	0.64	1.10	1.30		
3G	0.84	1.43	1.62		
4G	0.95	1.66	1.95		
5G	1.20	1.88	2.11		
6G	1.47	2.23	2.51		
7G	1.64	2.65	2.92		
8G	2.16	3.14	3.21		

### **MECHANICAL SPECIFICATIONS**

	Connector Type	Cable Tpye	Overall Length(m m/in)	Cable Length(m m/in)	Weight(g)	Color
W9017BD0100	I-PEX MHF4 or equivalent + SMA Female with Spring Washer	Ф0.81 MM Coaxial Cable, Black	116/4.57	100/3.94	3	Black
W9017BD0200			216/8.50	200/7.87	3.3	
W9017BD0250			266/10.47	250/9.84	3.5	

ENVIRONMENTAL SPECIFICATIONS					
Operating Temperature	-40 ~ 85° C				
Storage Temperature	-40 ~ 85° C				
RoHS Compliant	Yes				
Issue: 1901					



In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION

This document contains confidential and proprietary information of Pulse Electronics, Inc. (Pulse) and is protected by copyright, trade secret and other state and federal laws. Its receipt or possession does not convey any rights to reproduce, disclose its contents, or to manufacture, use or sell anything it may describe. Reproduction, disclosure or use without specific written authorization of Pulse is strictly forbidden.

2

RoHS




**Description:** MHF4 - SMA Female Jumper Cable

Series: Cable Assembly

PART NUMBER:W9017BDXXXX

### **MECHANICAL DRAWING**



Issue: 1901

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION



3




**Description:** MHF4 - SMA Female Jumper Cable

Series: Cable Assembly

PART NUMBER:W9017BDXXXX

## Attenuation vs Frequency



W9017/Attenuation

#### Issue: 1901

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION



4




**Description**: MHF4 - SMA Female Jumper Cable

Series: Cable Assembly

PART NUMBER:W9017BDXXXX

### CHARTS

## Return Loss of Port-SMA Female vs Frequency



### W9017/Port-SMA

#### Issue: 1901

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION



5




**Description**: MHF4 - SMA Female Jumper Cable

Series: Cable Assembly

PART NUMBER:W9017BDXXXX

### CHARTS

## Return Loss of Port-MHF4 vs Frequency



### W9017/Port-MHF4

#### Issue: 1901

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION



6



**Description**: MHF4 - SMA Female Jumper Cable

Series: Cable Assembly

PART NUMBER:W9017BDXXXX

### PACKAGING

Quantity: 20 PCS / Column PE bag, 2000 pcs / Box



Issue: 1901

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION





**Description**: MHF4 - SMA Female Jumper Cable


Series: Cable Assembly

PART NUMBER:W9017BDXXXX


ASSEMBLY

The SMA male connector fits through the assembly hole, the hole size is below. SMA connector thread length: 11mm / 0.43in

# Panel cut-out



Option 1



**Option 2** 

In the effort to improve our products, we reserve the right to make changes judged to be necessary. CONFIDENTIAL AND PROPRIETARY INFORMATION



8