

Mounting material - OCS POLEFIX 1210



1476926

<https://www.phoenixcontact.com/us/products/1476926>

Please be informed that the data shown in this PDF document is generated from our Online Catalog. Please find the complete data in the user documentation. Our General Terms of Use for Downloads are valid.

Mount for mast Ø of 60 mm ... 140 mm, complete set for a housing of 12" x 10", material: steel



Your advantages

- Internationally certified housing system
- Special plastic ensures safe continuous operation
- Provides protection against the ingress of jet water
- Withstands even heavy mechanical strain

Commercial Data

Item number	1476926
Packing unit	1 pc
Minimum order quantity	1 pc
Sales Key	A13
Product Key	ACFDBZ
GTIN	4063151897307
Weight per Piece (including packing)	1,070 g
Weight per Piece (excluding packing)	940 g
Customs tariff number	73269098
Country of origin	EE

Mounting material - OCS POLEFIX 1210



1476926

<https://www.phoenixcontact.com/us/products/1476926>

Technical Data

Product properties

Product type	Mounting material
Housing type	Outdoor housing
Housing series	OCS

Dimensions

Width	247 mm
Height	376 mm

Mounting

Mounting type	Mast mounting or wall mounting
---------------	--------------------------------

Mounting material - OCS POLEFIX 1210



1476926

<https://www.phoenixcontact.com/us/products/1476926>

Classifications

ECLASS

ECLASS-11.0	27182702
-------------	----------

Mounting material - OCS POLEFIX 1210



1476926

<https://www.phoenixcontact.com/us/products/1476926>

Accessories

Screwdriver

Screwdriver - SF-SLIC 1,6X10-175 - 1212555

<https://www.phoenixcontact.com/us/products/1212555>



Screwdriver, slot-headed, with impact cap, with hexagon wrench aid for open-end wrench and ring wrench, size: 1.6 x 10 x 175 mm, 2-component grip

Screwdriver

Screwdriver - SF-SLIC 1,2X7,0-125 - 1212554

<https://www.phoenixcontact.com/us/products/1212554>



Screwdriver, slot-headed, with impact cap, with hexagon wrench aid for open-end wrench and ring wrench, size: 1.2 x 7.0 x 125 mm, 2-component grip, with non-slip grip

Mounting material - OCS POLEFIX 1210



1476926

<https://www.phoenixcontact.com/us/products/1476926>

Tool set

Tool set - SF-SOCKET SET 47 - 1200292

<https://www.phoenixcontact.com/us/products/1200292>



1/4" socket set, 47-piece, 1/4" reversible ratchet, 48 teeth with fast locking system, 50 mm and 100 mm 1/4" extensions, 1/4" screwdriver handle, 150 mm 1/4" flexible extension, 1/4" Cardan joint, 1/4" T-handle
2 x 1/4" bit adapter, 13 knurled 1/4" sockets, wrench size: 4 / 4.5 / 5 / 5.5 / 6 / 7 / 8 / 9 / 10 / 11 / 12 / 13 / 14 mm, 21 knurled socket bits: 6 x Torx® T10, T15, T20, T25, T30, T40, 6 x Hex 3, 4, 5, 6, 7, 8 mm, 3 x Phillips recess® PH1, PH2, PH3, 3 x Pozidriv® PZ1, PZ2, PZ3, 3 x slotted 4, 5.5, 7 mm, Allen wrench Hex 1.27, 1.5, 2, 2.5 mm, breakage and impact-resistant plastic case with metal fastening

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com