

MPP ix Tp A 4x2xAWG26 Cat6A PVC out 1,0m



Part number	33 48 343 4806 010
Specification	MPP ix Tp A 4x2xAWG26 Cat6A PVC out 1,0m
HARTING eCatalogue	https://b2b.harting.com/33483434806010

Image is for illustration purposes only. Please refer to product description.

Identification

Category	System cabling
Series	HARTING Mini PushPull
Identification	ix Industrial [®]
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING Mini PushPull ix Industrial [®] Type A Overmoulded
Connector 2	HARTING Mini PushPull ix Industrial [®] Type A Overmoulded
Type of cable	Copper cable (round)
Description of the cable	UV resistant
Version	
Cable length	1 m
Number of cores	8
Core structure	4x 2x AWG 26/7
Termination method	IDC termination
Technical characteristics	
Transmission characteristics	Cat. 6 _A Class E _A up to 500 MHz

Page 1 / 2 | Creation date 2023-02-15 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Customised Solutions GmbH & Co. KG | In der Tütenbeke 22 | 32339 Espelkamp | Germany Phone +49 5772 47-0 | info@HARTING.com | www.HARTING.com



Technical characteristics

Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Limiting temperature	-20 +80 °C unmoved
	-20 +80 °C moved

Material properties

Material (cable)	PVC
Colour (cable)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 61076-3-124
O and a second state	
Commercial data	
Packaging size	1
Country of origin	Latvia
European customs tariff number	85444290
GTIN	5713140282889
eCl@ss	27060390 Ready-made data cable (unspecified)

Page 2 / 2 | Creation date 2023-02-15 | Please note that the data specified here were taken as extracts from the online catalogue. Please refer to the user documentation for the complete and up-to-date information and data. Please also note that the user is responsible for validating functionality, conformity with applicable laws and directives, as well as for the electrical safety in the particular application. HARTING Customised Solutions GmbH & Co. KG | In der Tütenbeke 22 | 32339 Espelkamp | Germany Phone +49 5772 47-0 | info@HARTING.com | www.HARTING.com