

# Crimp Tool Kit

## Frame, Dies, Tool Box

**multicomp**PRO

**RoHS  
Compliant**




### Description

MP009830 (Tool Kit) Ratchet Crimp Tool Kit,  
Interchangeable with 5 dies

### Features

- Rapid swap out die set by pushing screws without extra tools.
- Compatible with a wide range of die sets and fulfills most demands in termination applications.
- Leverage action requires less hand force;
- Full-cycle ratchet performs a complete and reliable crimp result.
- Built-in a safety release to quick unlock and eliminate mis-crimp.
- Ergonomic bi-component grips feature extreme comfort and reduce user fatigue during prolonged use.

### Ratchet Crimper (Tool Frame)



### Specification

- Length : 8.7" (220 ±3 mm)
- Weight : 556.6 g
- Material : Frame - Middle Carbon Steel
- Finished : Black Oxide Finished And Hardened
- Handle : Dual-Color
- Function : Quick Interchangeable Ratchet Crimper Frame

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
sg.element14.com/b/multicomp-pro






**multicomp**PRO

# Crimp Tool Kit

## Frame, Dies, Tool Box

**multicomp** PRO

### Kit Includes Dies:







|                                                                                     |                                                                                                                                                            |
|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|
|    | <p>Insulated Terminals<br/>           AWG 22-18/16-14/12-10<br/>           DIN 0.5-1.0/1.5-2.5/4-6 mm<sup>2</sup></p>                                      |
|    | <p>Non-insulated terminal or open barrel terminal<br/>           AWG 20-18/16-14/12-10<br/>           DIN 0.5-1/1.5-2.5/4-6mm<sup>2</sup></p>              |
|   | <p>Pin terminal insulated or non-insulated ferrules<br/>           AWG 20/18/17/16/14/12/10<br/>           DIN 0.5/0.75/1.0/1.5/2.5/4/6 mm<sup>2</sup></p> |
|  | <p>Non-insulated terminal<br/>           AWG 18-16/14/12-10/8<br/>           DIN 0.75-1.5/2.5/4-6/10 mm<sup>2</sup></p>                                    |
|  | <p>Insulated flag terminal<br/>           AWG 22-18/16-14<br/>           DIN 0.35-1.0/1.5-2.5 mm<sup>2</sup></p>                                           |

# Crimp Tool Kit

## Frame, Dies, Tool Box

**multicomp** PRO

### Additional Dies offered by Multicomp PRO (not included into this Kit):

|                                                                                     |                                                                                                                                    |
|-------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------|
|    | <p><b>MP009833</b><br/>RG58, 59, 62, 6<br/>.068"/.216"/.324"/.360"<br/>1.73/5.49/8.23/9.14mm</p>                                   |
|    | <p><b>MP009835</b><br/>Fiber Optic ST, SC, LC connectors<br/>.151"/.178"/.134"/.139"/.190"<br/>3.84/4.52/3.40/3.53/4.83mm</p>      |
|    | <p><b>MP009836</b><br/>SMA, SMB, SMC, MCX<br/>.043"/.069"/.100"/.128"/.151"/.213"<br/>1.09/1.75/2.54/3.25/3.84/5.41mm</p>          |
|  | <p><b>MP009837</b><br/>D-Sub terminals<br/>AWG 24-30/18-22<br/>DIN 0.25-0.05/1.0-0.35mm<sup>2</sup></p>                            |
|  | <p><b>MP009838</b><br/>Crimps Pin terminals, insulated or non-insulated ferrules<br/>AWG 4/2/6<br/>DIN 25/35/16 mm<sup>2</sup></p> |
|  | <p><b>MP009839</b><br/>Crimps Solar Terminals<br/>AWG 14/12/10<br/>DIN 2.5/4/6 mm<sup>2</sup></p>                                  |

### Part Number Table

| Description                                               | Part Number |
|-----------------------------------------------------------|-------------|
| Ratchet Crimp Tool Kit, Interchangeable, 5 Dies, Tool Box | MP009830    |

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro  
Farnell.com/multicomp-pro  
sg.element14.com/b/multicomp-pro

**multicomp** PRO