PANDUIT®

Product Bulletin

Corrugated Loom Clamps

Panduit corrugated loom clamps are designed to secure and route electrical cables, and hydraulic or pneumatic hoses in heavy duty vehicle applications. These products are produced with highly durable, light weight resins that have been tested to sustain the most challenging installations. Typical applications include but are not limited to heavy duty trucking, off road vehicles, agriculture and construction equipment, and electric vehicles (EV).





Ordering Information

Clamps are sold in packages of either 100 halves (50 complete clamps) or 250 halves (125 complete clamps). They come in different configurations for single, 2-position and 3-position and accommodate 5/8", 3/4", 7/8" and 1" corrugated loom tubing.

Part Number	Description	Package Qty.	Paired Clamps Qty.	Images (note, full paired clamp shown)	
CLC62X1S8TL370	1-Position 5/8" Corrugated Loom Clamp	250	125		
CLC75X1S8TL370	1-Position 3/4" Corrugated Loom Clamp				
CLC88X1S8TL370	1-Position 7/8" Corrugated Loom Clamp				
CLC100X1S8TL370	1-Position 1" Corrugated Loom Clamp				
CLC62X2S8TL370	2-Position 5/8" Corrugated Loom Clamp	250	125		
CLC75X2S8TL370	2-Position 3/4" Corrugated Loom Clamp				
CLC88X2S8TL370	2-Position 7/8" Corrugated Loom Clamp				
CLC100X2S8TL370	2-Position 1" Corrugated Loom Clamp				
CLC62X3S8C370	3-Position 5/8" Corrugated Loom Clamp	100	50	PE OF	
CLC75X3S8C370	3-Position 3/4" Corrugated Loom Clamp				
CLC88X3S8C370	3-Position 7/8" Corrugated Loom Clamp				
CLC100X3S8C370	3-Position 1" Corrugated Loom Clamp				

Technical Information

Continuous Use Temperature	Material	UL94 Flammability Rating	Channel spacing (center to center distance between cables)	Bolt size
-40C to 135C; -40F to 275F	Nylon 6.6, 13% Glass-filled, Heat Stabilized, for added strength during installation and for longevity in rugged environments	НВ	1.5" (38mm)	5/16 (M8)

WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT CANADA Markham, Ontario cs-cdn@panduit.com Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK cs-emea@panduit.com Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore cs-ap@panduit.com Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan cs-japan@panduit.com Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico cs-la@panduit.com Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia cs-aus@panduit.com Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to www.panduit.com/warranty

For more information



it us at youry panduit

Visit us at www.panduit.com

Contact Customer Service by email: cs@panduit.com or by phone: 800.777.3300 ©2022 Panduit Corp. ALL RIGHTS RESERVED. Printed in the U.S.A. CMCB5-WW-ENG 3/2022