

## Product information

# 00 21 50 S

## Tool backpack Modular X18 Plumbing



- Fits you and your tools: practical and comfortable due to fully hinged front and back, removable tool board and padding for your back
- As individual as you are: Optimal flexibility due to innovative FIDLOCK® connectors and MOLLE webbing
- Fit for any challenge: with two separate inner compartments for tools, measuring instruments, notebook or tablet
- Durable fabric made of sustainable recycled synthetic fibers, splash-proof and easy to clean
- Waterproof molded bottom made of impact-resistant plastic for a secure upright position when opened and closed, 6 cm high
- One MOLLE strap on the inside and four MOLLE straps on the outside for attaching any adapters, carabiners and accessories
- FIDLOCK® connections are fastened or unfastened in no time at all
- A total of 21 retaining loops and 37 pockets, some with zips
- Luggage strap for fixing to telescopic handles of tool cases
- 50 x 35 x 25 cm (H x W x D), empty weight 2.9 kg, tested load capacity up to 15 kg
- Equipped with 12 KNIPEX tools, a total of 17 brand tools, partly VDE-tested according to DIN EN 60900
- Max. payload: 15 kg
- Volume: 18 litres

### General

Article No.	00 21 50 S
EAN	4003773089070
Weight	6,550 g
Dimensions	340 x 210 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Dimension exterior (interior) width mm	340 mm
Dimension exterior (interior) height mm	210 mm
Dimension exterior (interior) depth mm	530 mm

### Content

00 11 01	1 x KNIPEX TwinKey® for all standard cabinets and shut-off systems
00 21 50 LE	1 x KNIPEX Modular X18 empty
74 06 180	1 x High Leverage Diagonal Cutter ⚠ 1000V 
86 03 300	1 x Pliers Wrench pliers and a wrench in a single tool 
87 01 180	1 x KNIPEX Cobra® High-Tech Water Pump Pliers 
87 01 300	1 x KNIPEX Cobra® High-Tech Water Pump Pliers 
90 10 165 BK	1 x KNIPEX CutiX® Universal knife
90 22 10 BK	1 x KNIPEX BiX® Cutter for plastic pipes and sealing sleeves
90 31 02 SB	1 x KNIPEX TubiX® Pipe cutter
98 20 35 SL	1 x Screwdriver (Slim) for slotted screws (3,5 mm)

<b>Content</b>	
	⚠ 1000V ⚡
98 20 55 SL	1 x Screwdriver (Slim) for slotted screws (5,5 mm) ⚠ 1000V ⚡
98 24 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Phillips® (PH1) ⚠ 1000V ⚡
98 24 02 SL	1 x Screwdriver (Slim) for cross-recessed screws Phillips® (PH2) ⚠ 1000V ⚡
01114	1 x Stabila Wooden folding rule type 1607, white, 2 m
101-0300	1 x Picard Locksmith's hammer (300 g)
2281	1 x Stabila spirit level type 70 (30 cm)
0022086	1 x Wera set of hex key wrenches (1,5 - 10 mm)

*technical change and errors excepted*