#### Kraftform Kompakt









EAN: 4013288220554

Part number:

Article number:

05059040001 Kraftform Kompakt VDE

Stainless 8 extra slim 1

Size:

Weight:

Country of origin:

**Customs tariff** 

190x90x60 mm

330 g CZ

82054000

number:

- Individually tested VDE Stainless blades, some of which with reduced blade diameter
- Individually tested tool as per IEC 60900 at 10,000 V
- Blades made of stainless steel to prevent extraneous rust
- Vacuum ice-hardening provides the required hardness and strength
- Multi-component VDE-insulated Kraftform handle with anti-roll feature
- Ergonomic Kraftform handle for low-fatigue working
- In robust folding bag with Wera 2go compatibility

7 VDE stainless blades, some of which with reduced blade diameter, so that even low-lying screw and spring elements can be easily reached and operated. One 3817 VDE Kraftform bitholding screwdriver for ergonomic screwdriving. In a robust pouch. Individually tested tools as per IEC 60900. Individually tested at 10,000 V for safe working at the approved voltage of 1,000 V. Wera's stainless steel tools are vacuum ice tempered and therefore have the hardness and strength properties required for screw connections. Industrial use is possible without restrictions. The pouch is suitable for attachment to walls, shelves, workshop trolleys and the Wera 2go system thanks to the hook and loop fastener system on the back.














#### Kraftform Kompakt








Solution to the rust problem: screwdriving stainless steel together with stainless steel! Wera stainless steel tools are manufactured out of stainless steel so unsightly rust can be avoided.

### Individually tested



Each Kraftform Kompakt VDE set has been tested individually at 10,000 volts, in accordance with IEC 60900.This ten-times-higher testing load guarantees safe working at their maximum permitted load of 1,000 volts.

VDE-insulated screwdriver with reduced blade diameter



Reduced blade diameter with integrated protective insulation, allows sunken screws and spring elements to be accessed and actuated, individually tested as per IEC 60900.

## Handle/interchangeable blade system – Kraftform Kompakt VDE

The Kraftform Kompakt series

stands for low weight, low space

requirements and high flexibility

due to interchangeable blades.



The handle/interchangeable blade system allows rapid exchange of the blades required for a wide range of applications.

## Easy exchange



Kraftform Kompakt VDE sets come with an insulated handle and insulated inter-changeable blades, that can be exchanged without any special tools.

## Multi-component handle



Wera produces the Kraftform handle out of several materials with different properties. A resistant plastic is used for the core which ensures that the blade is held securely even under high strain. A softer material is used for the coloured soft zones, which provides high frictional resistance and allows the transfer of high forces - resulting in less required screwdriving effort. The red sections with their hard surfaces prevent any "sticking" of the hand to the handle, making rapid repositioning of the hand possible.

#### **Prevents hand injuries**



The outstanding design of the Kraftform handle that fits perfectly into the hand prevents hand injuries such as blisters and calluses.

Web link

https://products.wera.de/en/news\_spring\_summer\_2023\_kraftform\_kompakt\_kraftform\_kompakt\_vde\_stainless\_8\_extra\_slim\_1.html

## Kraftform Kompakt VDE Stainless 8 extra slim 1, 8 pieces

### Kraftform Kompakt



#### Set contents:

### 3817 VDE Kraftform Stainless blade-holding handle, 9 x 98 mm

05003991001 1x 9 x 98 mm



# Kraftform Kompakt VDE 3067 i TORX®, stainless, TX 8 x 154 mm

1x TX 8 x 154 mm 1x TX 9 x 154 mm 1x TX 10 x 154 mm 1x TX 30 x 154 mm

## Kraftform Kompakt VDE 3067 iS TORX®, stainless, TX 15 x 154 mm

1x TX 15 x 154 mm 1x TX 20 x 154 mm 1x TX 25 x 154 mm

## Hook and Loop Fastener Strip 70, 50 x 70 mm

1x 50 x 70 mm

