

Grounding & Cleaning

If the material is used on top of an already properly grounded surface, grounding hardware may not be necessary. Where no properly grounded surface is available, grounding hardware is required to provide a path-to-ground. Rtg compliance verification measurements must be made as outlined in ESD TR53 with a surface resistance meter.

See Tech Bulletin $\underline{\mathsf{TB-7000}}$ for Reztore® Surface & Mat Cleaner Application Instructions.

Limited Lifetime Warranty:

Desco warrants for one year that Statfree® matting products will be free of defects in materials and workmanship and will guarantee dissipative/conductive mat properties for the life of the mat. Damage to matting caused by misuse of any kind, including using inappropriate cleaners is not covered by Desco Limited Warranty.

Desco Regualtory Statement

See the Desco Industries Regulatory Statement: http://www.descoindustries.com/pdf/Regulatory.pdf

See the Desco Limited Warranty:

http://desco.descoindustries.com/Limited-Warranty.aspx

See the Desco Disclaimer:

http://desco.descoindustries.com/Disclaimer.aspx

STATFREE® B2 PLUS DISSIPATIVE VINYL

Specifications

Standard Document Meets Requirements of:

ANSI/ESD S20.20 Worksurface

Electrical Properties Typical Values

Dissipative Surface LayerRtt Resistance:1 x 106 to < 1 x 109 ohms</td>ANSI/ESD S4.1 and ESD TR53Rtg Resistance:1 x 106 to < 1 x 109 ohms</td>ANSI/ESD S4.1 and ESD TR53

Ground Plane Layer

Rtt Resistance: < 1 x 10⁶ ohms ANSI/ESD S4.1 and ESD TR53

Physical Properties

Construction: Multi-layer vinyl, dissipative top layer, conductive mesh inner layer (x2),

Test Procedures/Method

conductive bottom laver

Thickness: 0.080" (2 mm), nominal ± 10%

Color:* Blue or Green (top side), Black (bottom side)
Texture:* KidGrain (top side), Textured (bottom side)
Hardness: 85 ± 5 Shore "A", per ASTM-D2240

Tolerances:

Width ± 0.250"

Length ± 0.250" every 1 linear foot of running material.

Thickness ±10%

Matting materials have a tendency to shrink slightly when first unrolled. In applications where length is critical, allow the material to condition for at least 4 hours before cutting to size. Always using care trim with a sharp knife or razor blade.

For product listings, Click Here

Made in the United States of America

STATFREE® B2 PLUS 3 LAYER VINYL ESD MATTING, 0.080" THICKNESS

Specifications and procedures subject to change without notice.



DESCO WEST: 3651 WALNUT AVE., CHINO, CA 91710 WEB SITE: <u>Desco.com</u> PHONE (909) 627-8178

DESCO EAST: ONE COLGATE WAY, CANTON, MA 02021-1407 PHONE (781) 821-8370

STATFREE® B2 PLUS DRAWING PM-134 DATE: April 2023

^{*}Color and texture may vary between lots and mills

^{**}Tray liners have 3/4" radius corners and do not include grounding hardware.