Industrial Mains Socket With Backshell

multicomp PRO

RoHS Compliant




Features


- Clamping cable fix
- With Backshell Structure

Specifications

6A / 32A
30V / 400V 50-60Hz
/4/5
244
6A : 1.5mm²
2A : 2.5mm²
6A : 4mm²
2A : 6mm²
Omm to 14mm / 13mm to 19mm

Diagram





Dimensions

Poles	3	4	5	3	4	5
а	59.5	67.5	74.5	82		88.5
b	158	160	162	191.5		193.5
d	83	92	99	9	9	106.5

Dimensions : Millimetres

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



Industrial Mains Socket With Backshell

multicomp PRO



Features


- Clamping cable fix
- With Backshell Structure

Specifications

Current Rating	: 16A / 32A
Voltage Rating	: 230V / 400V 50-60Hz
Poles	: 3 / 4 / 5
IP rating	: IP67
Min Wire Size	: 16A : 1.5mm ² 32A : 2.5mm ²
Max Wire Size	: 16A : 4mm ² 32A : 6mm ²
Cable outer diameter range	: 10mm to 13mm / 13mm to 19mm

Diagram





Dimensions

Poles	3	4	5	3	4	5
а	71	78	88.5	95.5		101.5
b	79	90.5	98	100.5		104
d	162	162.5	167	19	94	199.5

Dimensions : Millimetres

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



multicomp PRO

Part Number Table

Description	Part Number
Mains Socket w/ Backshell, 3P, 16A, 230V, IP44	MP011044
Mains Socket w/ Backshell, 3P, 16A, 230V, IP67	MP011080
Mains Socket w/ Backshell, 4P, 16A, 400V, IP44	MP011045
Mains Socket w/ Backshell, 4P, 16A, 400V, IP67	MP011081
Mains Socket w/ Backshell, 5P, 16A, 400V, IP44	MP011046
Mains Socket w/ Backshell, 5P, 16A, 400V, IP67	MP011082
Mains Socket w/ Backshell, 3P, 32A, 230V, IP44	MP011056
Mains Socket w/ Backshell, 3P, 32A, 230V, IP67	MP011092
Mains Socket w/ Backshell, 4P, 32A, 400V, IP44	MP011057
Mains Socket w/ Backshell, 4P, 32A, 400V, IP67	MP011093
Mains Socket w/ Backshell, 5P, 32A, 400V, IP44	MP011058
Mains Socket w/ Backshell, 5P, 32A, 400V, IP67	MP011094

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

