

RoHS
Compliant



Description

Every enclosure comes complete with everything you need in one kit. Manufactured from galvanised steel, each door enclosure & 2mm back plate comes with a 3 year guarantee against corrosion. Available in 21 sizes.

Kit Includes

- Galvanised Steel Wall Mounting Brackets
- Galvanised Mounting Plate
- Spacers for the Back Plate
- Pre-wired and Fitted Earthing Strap
- Stainless Steel Studs
- Metal Locks and Key supplied as Standard

Features

- IP66 & IK10 rated
- Pre-wired & fitted earth strap
- Gland plate with IP66 sealing gasket
- Compliance to IEC 60529 & CE certified
- Perforated steel back plate available
- 3 Year guarantee against corrosion
- Temperature rating -20°C to +55°C
- Colour Grey (RAL7035)

Product Code	H (mm)	W (mm)	D (mm)
MP011946	250	200	130
MP011947	300	200	130
MP011948	300	300	150
MP011949	350	250	150
MP011950	500	400	175
MP011951	400	300	170
MP011952	400	300	220
MP011953	400	400	200
MP011954	500	350	190
MP011955	500	400	200
MP011956	500	400	175
MP011957	500	400	240
MP011958	500	500	200
MP011959	600	400	200
MP011960	600	400	250
MP011961	600	600	200
MP011962	800	400	200
MP011963	700	500	250
MP011964	800	600	260
MP011965	1000	600	300
MP011966	1250	600	300

Part Number Table

Description	Part Number
Galvanised steel, IP66 & IK10	MP011946
Galvanised steel, IP66 & IK10	MP011947
Galvanised steel, IP66 & IK10	MP011948
Galvanised steel, IP66 & IK10	MP011949
Galvanised steel, IP66 & IK10	MP011950
Galvanised steel, IP66 & IK10	MP011951
Galvanised steel, IP66 & IK10	MP011952
Galvanised steel, IP66 & IK10	MP011953
Galvanised steel, IP66 & IK10	MP011954
Galvanised steel, IP66 & IK10	MP011955
Galvanised steel, IP66 & IK10	MP011956
Galvanised steel, IP66 & IK10	MP011957
Galvanised steel, IP66 & IK10	MP011958
Galvanised steel, IP66 & IK10	MP011959
Galvanised steel, IP66 & IK10	MP011960
Galvanised steel, IP66 & IK10	MP011961
Galvanised steel, IP66 & IK10	MP011962
Galvanised steel, IP66 & IK10	MP011963
Galvanised steel, IP66 & IK10	MP011964
Galvanised steel, IP66 & IK10	MP011965
Galvanised steel, IP66 & IK10	MP011966

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.