


[Check Stock/Pricing by Product No.](#)[Search By Size and Type](#)[Find a Distributor / Rep](#)

[Home](#) / [Products](#) / [NEMA / IP Rated Boxes](#) / [NBC Series Plastic NEMA Enclosure](#) / NEMA Enclosure with Concealed Hinge and Turn Latch NBC-10372

NEMA Enclosure with Concealed Hinge and Turn Latch NBC-10372



5 DAY
MOD

2 Videos

Model # NBC-10372

[NBC Series Plastic NEMA Enclosure](#)

- Non-metallic, wall-mounting plastic enclosure.
- Meets NEMA 1, 4, 4x and IEC529 IP 66 requirements.
- Use in wet/washdown, dirty and corrosive environments.

[Compare Sizes and Models](#)[See Accessories](#) [Request Modifications](#)[Check Stock / Pricing](#)

External Size L x W x D: 32.05" x 24.18" x 11.13"

Internal Size L x W x D: 30.67" x 22.82" x 10.60"



Weight: 27.5 lbs

Color: Light Gray

RoHS Certified: Always Compliant

Cover Style: Opaque, Hinged Cover

Indoor / Outdoor: Outdoor (UV Stabilized)

Flammability Rating: UL94-5VA

Door Flammability Rating: UL94-5VA

Type of Plastic: Poly PBT Blend

Door Type of Plastic: Poly PBT Blend

UL Rating: UL508

Gasket Type: Polyurethane

Service Temperature Min: -40°C

Service Temperature Max: 75°C



Help

NEMA Rating: NEMA 1, NEMA 4, NEMA 4X


IP Rating: 66

Mounting Style: Mounting Brackets

Latch Style: Turn Latch



DRAWING



OTHER MODELS IN THIS SERIES

-- Indoor / Outdoor --

-- Type of Plastic --

Model #	External Dimensions	Internal Dimensions	Indoor / Outdoor	Type of Plastic
NBC-10352	32.05" x 24.18" x 11.13"	30.67" x 22.82" x 10.60"	Indoor (Not UV Stabilized)	ABS Poly Blend
NBC-10372	32.05" x 24.18" x 11.13"	30.67" x 22.82" x 10.60"	Outdoor (UV Stabilized)	Poly PBT Blend

ACCESSORIES

Locking Hasp NBX-10915

NBX-10915

[View Details](#)

Air & Moisture Vent Style A NBX-10910

NBX-10910

[View Details](#)

[Check Stock / Pricing](#)

[Check Stock / Pricing](#)

RELATED PRODUCT SERIES



NBA Series Plastic NEMA Enclosure

[VIEW SERIES DETAILS](#)



NBD Series Plastic NEMA Enclosure

[VIEW SERIES DETAILS](#)



NBE Series NE

[VIEW SERIES D](#)



[440-946-3200](tel:440-946-3200) | [Find Distributor/ Rep](#) | [Contact Us](#)

[Warranty](#) [Privacy Policy](#) [Unsubscribe](#) ©2018 - 2023 BUD Industries, all rights reserved

