

[Check Stock/Pricing by Product No.](#)[Search By Size and Type](#)[Find a Distributor / Rep](#)

[Home](#) / [Products](#) / [General Use Boxes](#) / [ValuLine Series Chassis Enclosure](#) / ValuLine Series Aluminum Chassis Enclosure NHC-14150

ValuLine Series Aluminum Chassis Enclosure NHC-14150



2 Videos

Model # NHC-14150

[ValuLine Series Chassis Enclosure](#)

- Sides: 0.09-inch aluminum, white textured
- Front panel: 0.13 inch aluminum, natural
- Base, rear and top: 0.05 inch aluminum, smooth white
- Two detachable 11 gauge steel rack mounting brackets and rubber feet included
- Adhesive backed plastic film protects panels and provides surface for laying out position for drilling or punching
- Shipped unassembled

Finish:

[Compare Sizes and Models](#)

[Request Modifications](#)

[Check Stock / Pricing](#)

External Size H x W x D: 1.75" x 8.50" x 8.00"

Internal Size H x W x D: 1.65" x 8.25" x 7.75"



Weight: 1.7 lbs

Color: White Textured Powder Coated


Handles: No Handles



DRAWING



[? Help](#)



OTHER MODELS IN THIS SERIES

-- External Dimensions --

-- Internal Dimensions --

-- Handles --

Model #	External Dimensions	Internal Dimensions	Handles
HC-14098	1.75" x 17.00" x 13.00"	1.65" x 16.65" x 12.77"	Handles
NHC-14152	1.75" x 17.00" x 13.00"	1.65" x 16.69" x 12.75"	No Handles
HC-14097	1.75" x 17.00" x 8.00"	1.65" x 16.65" x 7.77"	Handles
NHC-14151	1.75" x 17.00" x 8.00"	1.65" x 16.69" x 7.75"	No Handles
NHC-14150	1.75" x 8.50" x 8.00"	1.65" x 8.25" x 7.75"	No Handles
HC-14100	3.50" x 12.75" x 13.00"	3.40" x 12.40" x 12.72"	Handles
HC-14101	3.50" x 17.00" x 13.00"	3.40" x 16.65" x 12.72"	Handles
NHC-14155	3.50" x 17.00" x 13.00"	2.75" x 16.69" x 12.75"	No Handles
HC-14099	3.50" x 17.00" x 8.00"	3.40" x 16.65" x 7.69"	Handles
NHC-14154	3.50" x 17.00" x 8.00"	2.75" x 16.69" x 7.75"	No Handles
NHC-14153	3.50" x 8.50" x 8.00"	2.75" x 8.25" x 7.75"	No Handles
HC-14102	5.25" x 12.75" x 13.00"	5.15" x 12.40" x 12.72"	Handles
HC-14103	5.25" x 17.00" x 13.00"	5.15" x 16.65" x 12.72"	Handles
NHC-14156	5.25" x 17.00" x 13.00"	4.50" x 16.69" x 12.75"	No Handles
HC-14104	7.00" x 17.00" x 13.00"	6.90" x 16.65" x 12.72"	Handles
NHC-14157	7.00" x 17.00" x 13.00"	6.25" x 16.69" x 12.75"	No Handles
HC-14105	8.75" x 17.00" x 13.00"	8.65" x 16.65" x 12.72"	Handles
HC-14106	10.50" x 17.00" x 13.00"	10.40" x 16.65" x 12.72"	Handles
HC-14107	10.50" x 17.00" x 15.00"	10.40" x 16.65" x 14.72"	Handles



Model #	External Dimensions	Internal Dimensions ⓘ	Handles
HC-14108	12.25" x 17.00" x 15.00"	12.15" x 16.65" x 14.72"	Handles
HC-14109	14.00" x 17.00" x 15.00"	13.90" x 16.65" x 14.72"	Handles



[440-946-3200](tel:440-946-3200) | [📍 Find Distributor/ Rep](#) | [Contact Us](#)

[Warranty](#) [Privacy Policy](#) [Unsubscribe](#) ©2018 - 2023 BUD Industries, all rights reserved

