

## Mobile Dunnage Platform Racks

NSF

Units can be used for moving case goods and other heavy items for cleaning, warehouse and stock room applications. Non-marking casters add flexibility. **Finish:** Gray Epoxy


Each unit consists of:

- 4 - 6" posts
- 1 - 3 sided frame
- 1 - dunnage shelf
- 4 - 5" swivel thermoplastic resin casters, 2 with brakes
- 4 - donut bumpers

**1,200 lb.**  
MOBILE LOAD CAPACITY

**NEW  
FINISH**

| GRAY <b>NEW</b><br>MODEL NO. | DIMENSIONS<br>W" x L" x H" | SHIP<br>WGT |
|------------------------------|----------------------------|-------------|
| M18366DGY                    | 18" x 36" x 12"            | 36 lbs      |
| M18486DGY                    | 18" x 48" x 12"            | 44 lbs      |
| M18606DGY                    | 18" x 60" x 12"            | 51 lbs      |
| M24366DGY                    | 24" x 36" x 12"            | 40 lbs      |
| M24486DGY                    | 24" x 48" x 12"            | 47 lbs      |
| M24606DGY                    | 24" x 60" x 12"            | 55 lbs      |



## Modular Dunnage Racks

NSF

Ideal for extreme load capacities (1,300-1,600 lb.). Includes tubular 1" square frame super structure and removable wire top mat. **Finish:** Gray Epoxy

Each unit consists of:

- 4 - 14" posts
- 1 - 3 sided frame
- 1 - dunnage shelf

**1,300-1,600 lb.**  
LOAD CAPACITY

**NEW  
FINISH**

| GRAY <b>NEW</b><br>MODEL NO. | DIMENSIONS<br>W" x L" x H" | SHIP<br>WGT |
|------------------------------|----------------------------|-------------|
| 183614DGY                    | 18" x 36" x 14"            | 28 lbs      |
| 184814DGY                    | 18" x 48" x 14"            | 36 lbs      |
| 186014DGY                    | 18" x 60" x 14"            | 43 lbs      |
| 243614DGY                    | 24" x 36" x 14"            | 32 lbs      |
| 244814DGY                    | 24" x 48" x 14"            | 39 lbs      |
| 246014DGY                    | 24" x 60" x 14"            | 47 lbs      |



## Tank & Beverage Container Racks

NSF

Represents a cost effective way to keep containers off the floor for cleanliness. This unit is an effective way to tidy up and increase available storage capacity. Used frequently in cafeterias and warehouse applications. **Finish:** Gray Epoxy

Each 1 Tier unit consists of:

- 4 - 34" posts
- 1 - 3 sided frame
- 1 - dunnage shelf

**1,300-1,600 lb.**  
LOAD CAPACITY

Each 2 Tier unit consists of:

- 4 - 54" posts
- 2 - 3 sided frames
- 2 - dunnage shelves

**2,600-3,200 lb.**  
LOAD CAPACITY

**NEW  
FINISH**

| GRAY <b>NEW</b><br>MODEL NO. | DIMENSIONS<br>W" x L" x H" | SHIP<br>WGT |
|------------------------------|----------------------------|-------------|
| <b>1 Tier</b>                |                            |             |
| 183634DGY                    | 18" x 36" x 34"            | 40 lbs      |
| 184834DGY                    | 18" x 48" x 34"            | 48 lbs      |
| 186034DGY                    | 18" x 60" x 34"            | 55 lbs      |
| 243634DGY                    | 24" x 36" x 34"            | 44 lbs      |
| 244834DGY                    | 24" x 48" x 34"            | 51 lbs      |
| 246034DGY                    | 24" x 60" x 34"            | 59 lbs      |
| <b>2 Tier</b>                |                            |             |
| 183654DGY                    | 18" x 36" x 54"            | 68 lbs      |
| 184854DGY                    | 18" x 48" x 54"            | 84 lbs      |
| 186054DGY                    | 18" x 60" x 54"            | 98 lbs      |
| 243654DGY                    | 24" x 36" x 54"            | 76 lbs      |
| 244854DGY                    | 24" x 48" x 54"            | 90 lbs      |
| 246054DGY                    | 24" x 60" x 54"            | 106 lbs     |



## Shelf Platform Racks

NSF

Represents an ergonomic solution for keeping case goods off the floor. Platforms are often used at workstations and prep storage areas. **Finish:** Chrome

Each unit consists of:

- 4 - 14" posts
- 1 - shelf

**600-800 lb.**  
LOAD CAPACITY PER SHELF

| CHROME<br>MODEL NO. | DIMENSIONS<br>W" x L" x H" | SHIP<br>WGT |
|---------------------|----------------------------|-------------|
| 183614PC            | 18" x 36" x 14"            | 14 lbs      |
| 184814PC            | 18" x 48" x 14"            | 18 lbs      |
| 186014PC            | 18" x 60" x 14"            | 21 lbs      |
| 243614PC            | 24" x 36" x 14"            | 17 lbs      |
| 244814PC            | 24" x 48" x 14"            | 20 lbs      |
| 246014PC            | 24" x 60" x 14"            | 25 lbs      |

