


Cable clip, Ø3.2 mm, Dmax=3.0mm, L=26.0mm, W=23.0mm, H=6.5mm, natural, 100pcs.

Art.-No. 151-22819 | TY8H1-PA66-NA | [Details](#)



- Designed to hold cables, tubes or conduits without cable tie
- Simply screwed or stuck (TY8H1S) onto panel
- Side gripping fingers exert firm hold but allow for easy cable removal



More products in this product group:

[Self Adhesive / Screw Fixing Clips >](#)

Base Data

Application	Ideal for holding ribbon cables in computer equipment, gaming machines or domestic appliances.
Colour	Natural (NA)
Fixation Method	screw-hole
Material	Polyamide 6.6 (PA66)
Pack Cont.	100 pcs.
Package Content packed in	pcs.
PART DESCRIPTION	TY8H1-PA66-NA
Product Family	TY8H1 with flat design
Product Group	Self Adhesive / Screw Fixing Clips
Short Description	Fixing Screw with flat design 26x24 mm natural
Variant	Closed




Product Dimensions

Bundle Diameter max (metric)	3.0 mm
Bundle Ø	3.0 mm
for Hole Ø (FH)	3.2 mm
Height (H)	6.5 mm
Length (L)	26.0 mm
Nominal Ø	3 mm
Weight/Unit	0.001141 kg
Width (W)	23.0 mm

Specifications

ELV compliant (Article 4 - 2)	YES
Flammability	UL 94 V2
Hazardous good	No
Operating Temperature	-40 °C to +85 °C
Specifications	
UV-Stabilised (Yes/No)	No

Logistics and Packaging



Country of Origin	DE
Customs Number	39269097
GTIN-13 / EAN	4031026122304
Order Unit	pcs.
Packaging 1 - Height (m)	0.03 m
Packaging 1 - Length (m)	0.26 m
Packaging 1 - Qty	100

Packaging 1 - Type	bag
Packaging 1 - Volume (m³)	0.00101 m³
Packaging 1 - Weight (kg)	0.1211 kg
Packaging 1 - Width (m)	0.13 m
Packaging 3 - Height (m)	0.171 m
Packaging 3 - Length (m)	0.56 m
Packaging 3 - Qty	2000
Packaging 3 - Type	box
Packaging 3 - Volume (m³)	0.0172 m³
Packaging 3 - Weight (kg)	2.642 kg
Packaging 3 - Width (m)	0.18 m
Packaging 4 - Height (m)	1.17 m
Packaging 4 - Length (m)	1.2 m
Packaging 4 - Qty	96000
Packaging 4 - Type	pallet
Packaging 4 - Volume (m³)	1.123 m³
Packaging 4 - Weight (kg)	147.816 kg
Packaging 4 - Width (m)	0.8 m

More Information

ETIM 7.0 Key	EC000127
ETIM 8.0 Key	EC000127
UNSPSC Key	39121702

