



Type label identification, laser printer

Helatag 1102 (Yellow)

These yellow labels come in various sizes and are ideal for the identification of industrial assets.

The labels can be easily printed with office laser printers. All label templates are already stored in HellermannTyton's TagPrint Pro software so label design including barcodes or logos has been made easy even with office printers.


Features and benefits

- Yellow rating labels for component marking and control cabinets
- For use on flat and smooth surfaces
- Crisp and clear text, barcodes and graphics
- Simple and efficient label design and printing with TagPrint Pro labelling software
- Templates available from www.HellermannTyton.com for those wishing to use MS Word
- Clear protective box to ensure labels stay as good as new



Optimal print results with a range of office laser printers.

MATERIAL	Type 1102, Polyester, yellow (1102)
Operating Temperature	-40 °C to +150 °C
Curing Temperature	from 0 °C
Adhesive	Acrylic
Thickness of Foil	55 µm
Chem. Material Properties	Excellent resistance against water, alcohol, most oils, lubricants, fuels, aliphatic solvents, weak acid, salts, alkalis and UV light.



TYPE	Width (W)	Height (H)	Labels per Sheet	Sheets per Pack	Pack Cont.	Colour	Article-No.
TAG156LA4-1102-YE	10.2	10.2	532 pcs.	19 pcs.	10,000 pcs.	Yellow (YE)	594-61102
TAG122LA4-1102-YE	15.0	9.0	372 pcs.	27 pcs.	10,000 pcs.	Yellow (YE)	594-21102
TAG120LA4-1102-YE	15.2	6.4	528 pcs.	19 pcs.	10,000 pcs.	Yellow (YE)	594-01102
TAG154LA4-1102-YE	17.0	9.0	341 pcs.	30 pcs.	10,000 pcs.	Yellow (YE)	594-51102
TAG124LA4-1102-YE	19.0	11.0	260 pcs.	20 pcs.	5,000 pcs.	Yellow (YE)	594-41102
TAG13LA4-1102-YE	19.1	6.4	440 pcs.	23 pcs.	10,000 pcs.	Yellow (YE)	594-31102
TAG121LA4-1102-YE	20.0	8.0	315 pcs.	32 pcs.	10,000 pcs.	Yellow (YE)	594-11102
TAG62LA4-1102-YE	31.8	9.5	180 pcs.	28 pcs.	5,000 pcs.	Yellow (YE)	594-81102
TAG171LA4-1102-YE	210.0	297.0	1 pc.	25 pcs.	25 pcs.	Yellow (YE)	594-71102

All dimensions in mm. Subject to technical changes.
Minimum Order Quantity (MOQ) may differ from package content. Other packaging options may also be available.



For product specific approvals and specifications please refer to the Appendix.



Add items to your watchlist!
www.HT.click/9-513

