## Human Machine Interface Touch Screen, 10.2" multicomp

### RoHS Compliant

#### **Specifications**

	Mode	MP011745	
Main	OS	Linux 4.9.11 QT based	
Wam	Processor	Cortex A7 528MHz	
	Size	10.2"	
	Screen	TFT	
	Resolution	1024 × 600	
Diamlar	Color	16,000k colors	
Display	Brightness (cd/m <sup>2</sup> )	300	
	Backlight	LED	
	Backlight Lifetime	50,000 hours	
	Touch Panel	High precision four-wire resistive	
	Memory	128 MB	
Storage	Flash	128 MB	
	SD Card Slot		
	USB Port	USB2.0 Host + USB2.0 Client	
RTC	Real-time clock	Yes	
RIC	Calendar	Yes	
	COM1	CN1:RS422/RS485 CN2: RS232	
	COM2		
I/O Port	COM3		
	Ethernet		
	CAN open		
	Rated Power	< 10W	
Power	Power Voltage	DC 24V	
	Input range	DC 12V to 28V	
	Shell Color	Grey	
	Shell Material	PC+ABS	
Enclosure	Overall Size (mm)	272.0W × 190.0H × 41.5D	
Enclosure	Mounting Size (mm)	260.0W × 179.0H	
	Mounting Method	Panel Mount	
	Weight (Kg)	1.31	

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



# Human Machine Interface Touch Screen, 10.2" multicomp

	Mode	MP011745	
	Working Temperature	-10°C to 60°C	
	Storage Temperature	-20°C to 70°C	
Environment	Humidity	10% to 85% RH (Non-condensing)	
	Vibration Resistance	17 ~ 25 Hz (X, Y, Z direction 2G/30 minutes)	
	Cooling	Air Cooling	
	Programming	PI Studio	
	Remote Access		
Software	Email Alarm		
Sollware	IP Camera		
	Audio Output		
	Video Player		
	IP Code	IP65 (Front panel)	
Certificates	CE	CE Marked	
Certificates	FCC	FCC Class A	
	UL		





Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro



### Human Machine Interface Touch Screen, 10.2" multicomp

#### Dimension





### Part Number Table

Description	Part Number
HMI-Touch Screen, 1024 × 600	MP011745

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

