Human Machine Interface Touch Screen, 7"

multicomp PRO



RoHS Compliant

Model			MP011739
General	Screen Size		7 Inch
	Resolution		800 × 480
	Colors		16,000K colors
	Brightness		250cd/m ²
	Backlight Type		LED
	Touch Panel		High procision four-wire resistive
	Backlight Life Time		50,000 hours
	CPU		Cortex A7 528MHz
	Storage		128M FLASH + 128M DDRIII RAM
	USB Port		USB host + USB Client
	СОМ	COM1	RS422/RS485
		COM2	RS232
Power	Power		<8w
	Power Supply		DC 24V (12~28V DC)
	Shell Material		PC+ABS
Dimension	Over size (mm)		201.2W × 147.2H × 39.0D
Birriorioion	Mounting size (mm)		192.0W × 138.0H
	Net/Weights (KG)		0.51/0.74
Operate Environment	Temperature		Working Temperature : -10°C to 60°C ; Storage Temperature : -20°C to 70°C
	Humidity		10-85%RH (Non-condensing)
	Seismic Resistance		IEC61131-2 standard Continuous vibration occasion: 10Hz~57Hz 0.075m m, 57Hz~150Hz 9.8m/s2 Discontinuous vibration: 10Hz~57Hz 0.035mm, 57H z~150Hz 4.9m/s2 X, Y, Z in 10 directions each (80 minutes)
	Cooling		Air cooling
IP Code			IP65 (Front panel)
CE			CE Marked
FCC			FCC Class A

Part Number Table

Description	Part Number
HMI-Touch Screen, 12-24V DC, Panel Mount	MP011739

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

