multicomp PRO

RoHS Compliant

Specifications

Туре	: Housing Type, Phenolic Height 12mm Phenolic Housing and Shield Material		
Max. Off Temperature	: 85°C		
Max. On Temperature	: 100°C		
Rated Current	: 15/16 Amps		
Terminal Selection	: 6.3mm×0.8mm, 90° Angle & Nickel Plated Brass 6.3mm×0.8mm, 0° Angle & Nickel Plated Brass		
Switch Type	: Close on rise (Normally Open)		

Part Number Table

Description	Туре	Temperature		Part Number
Automatic Reset Thermostat	N/O	Set 40°C ±3°C	Reset 25°C ±5°C	MP-11-25/40/E121B14H22K
	N/O	Set 50°C ±3°C	Reset 35°C ±5°C	MP-11-35/50/E121B14H22K
	N/O	Set 60°C ±3°C	Reset 45°C ±4°C	MP-11-45/60/E121B14H22K
	N/O	Set 70°C ±3°C	Reset 55°C ±5°C	MP-11-55/70/E121B14H22K
	N/O	Set 80°C ±3°C	Reset 65°C ±5°C	MP-11-65/80/E121B14H22K
	N/O	Set 90°C ±3°C	Reset 75°C ±5°C	MP-11-75/90/E121B14H22K
	N/O	Set 100°C ±3°C	Reset 85°C ±5°C	MP-11-85/100/E121B14H22K
	N/O	Set 40°C ±3°C	Reset 25°C ±5°C	MP-11-25/40/E111B14H22K
	N/O	Set 50°C ±3°C	Reset 35°C ±5°C	MP-11-35/50/E111B14H22K
	N/O	Set 60°C ±3°C	Reset 45°C ±4°C	MP-11-45/60/E111B14H22K
	N/O	Set 70°C ±3°C	Reset 55°C ±5°C	MP-11-55/70/E111B14H22K
	N/O	Set 80°C ±3°C	Reset 65°C ±5°C	MP-11-65/80/E111B14H22K
	N/O	Set 90°C ±3°C	Reset 75°C ±5°C	MP-11-75/90/E111B14H22K
	N/O	Set 100°C ±3°C	Reset 85°C ±5°C	MP-11-85/100/E111B14H22K

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro sg.element14.com/b/multicomp-pro

