, solder terminal, insulated, 2-pole, Audio Plug/Sockets, 2.5 mm



ielded 4831.1200
atasheet, General Product Information, Distributor- request for product

2.5 mm	Allowable Operation Tempe-	-20°C to 70°C
2-pole	rature	
0.5 A / 30 VDC	Terminal	solder terminal nickel-plated
0.5 A / 30 VAC	Housing	insulated
500 VDC	Style	straight
> 100 MΩ @ 500 VDC	Lifetime	5000 Insertions
	2-pole 0.5 A / 30 VDC 0.5 A / 30 VAC 500 VDC	2-polerature0.5 A / 30 VDCTerminal0.5 A / 30 VACHousing500 VDCStyle

Approvals and Compliances

Detailed information on product approvals, code requirements, usage instructions and detailed test conditions can be looked up in Details about Approvals


SCHURTER products are designed for use in industrial environments. They have approvals from independent testing bodies according to national and international standards. Products with specific characteristics and requirements such as required in the automotive sector according to IATF 16949, medical technology according to ISO 13485 or in the aerospace industry can be offered exclusively with customer-specific, individual agreements by SCHURTER.

Compliances

The product complies with following Guide Lines

Identification	Details	Initiator	Description
RoHS	RoHS	SCHURTER AG	Directive RoHS 2011/65/EU, Amendment (EU) 2015/863
(1)	China RoHS	SCHURTER AG	The law SJ / T 11363-2006 (China RoHS) has been in force since 1 March 2007. It is similar to the EU directive RoHS.
REACH	REACH	SCHURTER AG	On 1 June 2007, Regulation (EC) No 1907/2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals 1 (abbreviated as "REACH") entered into force.

Dimensions [mm]



Cable diameter max. 4.0 mm

4831.1210

All Variants

Product group	Diameter [mm]	Number of Poles	Terminal	Order Number	
Audio Plug/Sockets	2.5	2-pole	solder terminal	4831.1210	
Most Popular.					

Availability for all products can be searched real-time:https://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER

Packaging unit 100 Pcs

Mating Outlets/Connectors

Category / Description



Audio Plug/Sockets Overview complete

, solder terminal, screened, 2-pole, Audio Plug/Sockets, 2.5 mm	4831.2200
, PCB terminals, screened, 2-pole, Audio Plug/Sockets, 2.5 mm	4831.2220
, PCB terminals, insulated, 2-pole, Audio Plug/Sockets, 2.5 mm	4831.2230
, solder terminal, insulated, 2-pole, Audio Plug/Sockets, 2.5 mm	4831.3200