





Applications	Automotive Grade	
Feature	AEC-Q200 AEC-Q200  Wire Wound Wire Wound  Shield Magnetic Shield  Ferrite Core	
Series   Type	VLM	
Status	Production	
Brand	TDK	



	Size
Length(L)	13.50mm ±0.50mm
Width(W)	12.20mm ±0.50mm
Thickness   Height	7.80mm ±0.50mm
Recommended Land Pattern (A)	2.45mm Nom.
Recommended Land Pattern (B)	5.40mm Nom.
Recommended Land Pattern (C)	3.40mm Nom.
Recommended Land Pattern (D)	6.00mm Nom.
Recommended Land Pattern (E)	3.30mm Nom.
Recommended Land Pattern (F)	3.00mm Nom.

Electrical Characteristics				
Inductance	820nH ±20% at 100kHz			
Rated Current (L Change) [Typ.]				
Rated Current (L Change) [Max.]	36A (30% Down)			
Rated Current (Temperature Rise) [Typ.]	12.6A (20°C Rise)			
Rated Current (Temperature Rise) [Max.]				
DC Resistance [Typ.]	1.7mΩ			
DC Resistance [Max.]	2mΩ			
Self Resonant Frequency [Min.]				
Self Resonant Frequency [Typ.]				
Q [Min.]				
Q [Typ.]				

Other		
Operating Temp. Range (Including Self-Temp. Rise)	-40 to 150°C	
Soldering Method	Reflow	
Soldering Method	Iron Soldering	

<sup>!</sup> Images are for reference only and show exemplary products. ! This PDF document was created based on the data listed on the TDK Corporation website.

 $<sup>! \ \</sup>mbox{All specifications}$  are subject to change without notice.









AEC-Q200	YES
Packing	Embossed (Plastic)Taping [330mm Reel]
Package Quantity	400pcs
Weight	3.9g

<sup>!</sup> Images are for reference only and show exemplary products. ! This PDF document was created based on the data listed on the TDK Corporation website.


 $<sup>! \ \</sup>mbox{All specifications}$  are subject to change without notice.











## Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)











<sup>!</sup> Images are for reference only and show exemplary products.

<sup>!</sup> This PDF document was created based on the data listed on the TDK Corporation website.


 $<sup>! \ \</sup>mbox{All specifications}$  are subject to change without notice.







# **Associated Images**



<sup>!</sup> This PDF document was created based on the data listed on the TDK Corporation website.

 $<sup>! \ \</sup>mbox{All specifications}$  are subject to change without notice.