

Data sheet | Item number: 280-325

End and intermediate plate; 5 mm thick; gray

www.wago.com/280-325



Data

Physical data

| | |
|--------|----------------------|
| Width | 5 mm / 0.197 inches |
| Height | 93 mm / 3.661 inches |
| Depth | 28 mm / 1.102 inches |

Material Data

| | |
|-----------------------------|--|
| Note (material data) | Information on material specifications can be found here |
| Color | gray |
| Material group | I |
| Insulation material | Polyamide (PA66) |
| Flammability class per UL94 | V0 |
| Fire load | 0.121 MJ |
| Weight | 4 g |

Environmental requirements

| | |
|----------------------------------|-----------------|
| Processing temperature | -35 ... +85 °C |
| Continuous operating temperature | -60 ... +105 °C |

Commercial data

| | |
|---------------|----------------------------------|
| Product Group | 1 (Rail Mounted Terminal Blocks) |
|---------------|----------------------------------|

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.

| | |
|-----------------------|---------------|
| eCl@ss 10.0 | 27-14-11-33 |
| eCl@ss 9.0 | 27-14-11-33 |
| ETIM 8.0 | EC000886 |
| ETIM 7.0 | EC000886 |
| PU (SPU) | 25 pcs |
| Packaging type | box |
| Country of origin | DE |
| GTIN | 4017332150354 |
| Customs tariff number | 8538909990 |

Environmental Product Compliance

| | |
|------------------------|-------------------------|
| RoHS Compliance Status | Compliant, No Exemption |
|------------------------|-------------------------|

Required accessories

End plate

Terminal block for matrix patching



Item no.: 280-675

Double potential terminal block; 2,5 mm²; center marking; for DIN-rail 35 x 15 and 35 x 7.5; CAGE CLAMP®; 2,50 mm²; gray

www.wago.com/280-675

Downloads

Documentation

Bid Text

| | | | |
|------------------------|-------------|----------------|----------|
| 280-325 X81 - Datei | 19 Feb 2019 | xml 2.6 kB | Download |
| 280-325 doc - Datei | 18 Aug 2017 | doc 23.6 kB | Download |

Additional Information

| | | | |
|--|--|---------------|----------|
| | | pdf 2.2 MB | Download |
|--|--|---------------|----------|

CAD/CAE-Data

CAD data

| | | |
|----------------------|-----|----------|
| 2D/3D Models 280-325 | URL | Download |
|----------------------|-----|----------|

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG
 Hansastr. 27
 32423 Minden
 Phone: +49571 887-0 | Fax: +49571 887-169
 Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
 We are always happy to take your call at +49 (571) 887-44222.



CAE data

| | | |
|---------------------------|---------------------|--------------------------|
| EPLAN Data Portal 280-325 | URL | Download |
| WSCAD Universe 280-325 | URL | Download |
| ZUKEN Portal 280-325 | URL | Download |

Environmental Product Compliance

Compliance Search

| | | |
|--|---------------------|--------------------------|
| Environmental Product Compliance 280-325 End and intermediate plate; 5 mm thick; gray | URL | Download |
|--|---------------------|--------------------------|

Installation Notes

Subject to changes. Please also observe the further product documentation!