

Formed Steel Rack Panels

PBFS Series

Also referred to as a Spacer Blank Panel

Features



- Constructed of 16-gauge steel.
- Fits standard EIA-compliant rails.
- Install in unused rack space to improve both cooling efficiencies and prevent air re-circulation.
- Finished in smooth powder paint.
- TAA-compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America.




Note: We are reducing our offering to focus on 1U up to 10U. Larger sizes are available by special order. Minimums apply.



Accessories

- Mounting Hardware



We are making changes to the design of this product.

We are enclosing the rack mounting holes and rounding all edges.

Old Design (Left) | New Design (Right)



Part No.	Part No.	Part No.	Part No.	Part No.	Panel Height		Qty of
RAL9005	RAL9005	ANSI61	RAL7035	RAL9003	Rack	Panel	Mounting
Semi-Gloss Black	Matte Black	Dark Gray	Light Gray	Matt White	Units	Height	Points
-	PBFS19000BK	-	-	-	1/2U	0.09	2

Part No.	Part No.	Part No.	Part No.	Part No.	Panel Height		Qty of
RAL9005	RAL9005	ANSI61	RAL7035	RAL9003	Rack	Panel	Mounting
Semi-Gloss Black	Matte Black	Dark Gray	Light Gray	Matt White	Units	Height	Points
PBFS19001BK2	PBFS19001BK	PBFS19001GY2	PBFS19001LG2	PBFS19001WH	1U	1.75	4
PBFS19003BK2	PBFS19003BK	PBFS19003GY2	PBFS19003LG2	PBFS19003WH	2U	3.50	4
PBFS19005BK2	PBFS19005BK	PBFS19005GY2	PBFS19005LG2	PBFS19005WH	3U	5.25	4
PBFS19007BK2	PBFS19007BK	PBFS19007GY2	PBFS19007LG2	PBFS19007WH	4U	7.00	4
PBFS19008BK2	PBFS19008BK	PBFS19008GY2	PBFS19008LG2	PBFS19008WH	5U	8.75	4
PBFS19010BK2	PBFS19010BK	PBFS19010GY2	PBFS19010LG2	PBFS19010WH	6U	10.50	8
PBFS19012BK2	PBFS19012BK	PBFS19012GY2	PBFS19012LG2	PBFS19012WH	7U	12.25	8
PBFS19014BK2	PBFS19014BK	PBFS19014GY2	PBFS19014LG2	PBFS19014WH	8U	14.00	8
PBFS19015BK2	PBFS19015BK	PBFS19015GY2	PBFS19015LG2	PBFS19015WH	9U	15.75	8
PBFS19017BK2	PBFS19017BK	PBFS19017GY2	PBFS19017LG2	PBFS19017WH	10U	17.50	8

Clearance (While supplies last)

Part No.	RAL9005	Part No.	ANSI61	Part No.	RAL7035	
RAL9005	Remaining	ANSI61	Remaining	RAL7035	Remaining	Rack
Semi-Gloss Black	Stock	Dark Gray	Stock	Light Gray	Stock	Units
PBFS19019BK2	0	PBFS19019GY2	0	PBFS19019LG2	2	11U
PBFS19021BK2	15	PBFS19021GY2	0	No Option		12U
PBFS19022BK2	0	PBFS19022GY2	0	PBFS19022LG2	0	13U
PBFS19024BK2	8	PBFS19024GY2	0	No Option		14U
PBFS19026BK2	0	PBFS19026GY2	1	No Option		15U
PBFS19028BK2	4	PBFS19028GY2	0	No Option		16U
PBFS19031BK2	0	PBFS19031GY2	0	No Option		18U

Stock levels were last updated on June 12, 2023

Tags: **Flanged, Folded**

Data subject to change without notice