



MASTER Ultra Efficient LED bulb

MAS LEDBulbND4-60W E27 830 A60 FR G UE

This is the most efficient LED bulb from Philips brand. 210lm/W helps to concrete the company statement of sustainability. 50000 hour lifetime helps to extend the replacement cycle to reduce the waste. This is not only a high SPEC product, but also keeps the light quality of Philips brand

Product data

General information	
Lighting Technology	LED
Flux measurement reference	Sphere
Switching Cycle	50,000
Nominal lifetime	50,000 h
Cap base	E27 [E27]
Light technical	
Colour Code	830 [CCT of 3000K]
Luminous Flux	840 lm
Colour designation	White (WH)
Correlated Colour Temperature	3000 K
Luminous Efficacy (rated) (Nom)	210 lm/W
Colour consistency	<6
Colour rendering index (CRI)	80
LLMF at end of nominal lifetime (nom.)	70 %
Flickering value (PstLM)	1
Stroboscopic effect	0.4


Operating and electrical	
Line Frequency	50 to 60 Hz
Input frequency	50 to 60 Hz
Power Consumption	4 W
Lamp current (nom.)	45 mA
Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.4
Voltage (nom.)	220-240 V
Temperature	
T-Case maximum (nom.)	70 °C
Controls and dimming	
Dimmable	No
Mechanical and housing	
Lamp Finish	Frosted

MASTER Ultra Efficient LED bulb

Bulb shape	A60 [A 60 mm]
Approval and application	
Energy Efficiency Class	A
Energy consumption kWh/1,000 hours	4 kWh
EPREL registration number	1370036
CE mark	Yes
EU RoHS compliant	Yes
Product data	
Full EOC	871951443579700



Order product name	MAS LEDBulbND4-60W E27 830 A60 FR G UE
Order code	43579700
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
Material number (12NC)	929003480002
Full product name	MAS LEDBulbND4-60W E27 830 A60 FR G UE
EAN/UPC – Case	8719514435803

Dimensional drawing



Product	D	C
MAS LEDBulbND4-60W E27 830 A60 FR G UE	60 mm	105 mm

Photometric data




General uniform lighting - MAS LEDBulbND4-60W E27 830 A60 FR G UE

Light Distribution Diagram - MAS LEDBulbND4-60W E27 830 A60 FR G UE


MASTER Ultra Efficient LED bulb

Photometric data




Spectral Power Distribution Colour - MAS LEDBulbND4-60W E27 830 A60
FR G UE

Lifetime



Life Expectancy Diagram - MAS LEDBulbND4-60W E27 830 A60 FR G UE



Lumen Maintenance Diagram - MAS LEDBulbND4-60W E27 830 A60 FR G UE

