
*75A HIGH POWER CONTACTS WITH CRIMP, SOLDER BUCKET, AND PCB TERMINATIONS

Amphenol's D-Subminiature connectors are part of an industry standard for applications requiring robust and reliable connectors. These proven D-Subminiature connectors are one of the most popular Input/Output interconnects, addressing a wide variety of applications in Telecommunications, Data, Consumer, Industrial, Military, Instrumentation and Medical.

Our high power D-Sub connectors with *75A current rating is available in cable (Solder/Crimp) and board versions.

Note: * Denotes that the connectors confirm to UL1977 spec (T-Rise at rated current below RTI value of housing material).



FEATURES

- Various layout 2V2 to 8W8
- Available in Solder Bucket, Crimp and Right Angled versions
- Various PCB mounting accessories
- Lead-free and RoHS compliant

BENEFITS

- Product range to meet customer requisites
- To support cable and PCB mounting requirements
- Wide variety of choices for secure connections
- Meets environmental, health and safety requirements

GENERAL CHARACTERISTICS


Male Connector Layout

Shell Size	Layout	
É	2V2	•
А	3W3	***
	3V3	600
В	5W5	("O"O"O"O "O
C	8W8	


Power Contacts

DERATING CURVES

DERATING CURVE ON Connector DC8W8S500A9KLF





DERATING CURVE ON Connector DC8W8SA009KLF with Crimp Contact 8638PSC7506LF





DERATING CURVES

2V2,3V3,3W3,5W5,8W8 to be added











PART NUMBER SELECTOR

High Power-Cable Connector-Nomenclature



High Power-RA PCB Connector



PART NUMBERS

Description	Part Numbers
High Power, 3W3, Male cable connector	DA3W3PA009KLF
High Power, 3W3, Female cable connector	DA3W3SA009KLF
High Power, 5w5, Male cable connector	DB5W5PA009KLF
High Power, 5w5, Female cable connector	DB5W5SA009KLF
High Power, 3W3, Male R/A Board connector	DAV3W3P500H9KLF
High Power, 3W3, Female R/A Board connector	DAV3W3S500H9KLF
High Power, 5W5, Male R/A Board connector	DBV5W5P500H9KLF
High Power, 5W5, Female R/A Board connector	DBV5W5S500H9KLF
Female Power Contact, 75A*, Crimp Type	8638PSC7506LF
Male Power Contact, 75A*, Crimp Type	8638PPC7506LF
Female Power Contact, 75A*, Solder Bucket	8638PSS7506LF
Male Power Contact, 75A*, Solder Bucket	8638PPS7506LF