



CorePro LEDbulb



CoreProLEDbulb ND 7.5-60W A60 B22 930 UK

LEDbulbs are compatible with existing fixtures with an E27 holder and are designed for retrofit replacement of incandescent bulbs.

Product data

General information	
Lighting Technology	LED
Flux measurement reference	Sphere
Switching Cycle	50,000
Nominal lifetime	15,000 h
Cap base	B22 [B22]
Light technical	
Colour Code	930 [CCT of 3000K]
Beam angle (nom.)	180 degree(s)
Luminous Flux	806 lm
Colour designation	White (WH)
Correlated Colour Temperature	3000 K
Luminous Efficacy (rated) (Nom)	107 lm/W
Colour consistency	<6
Colour rendering index (CRI)	90
LLMF at end of nominal lifetime (nom.)	70 %
Flickering value (PstLM)	1
Stroboscopic effect	0.4
Operating and electrical	
Line Frequency	50 Hz
Input frequency	50 Hz
Power Consumption	7.5 W
Lamp current (nom.)	60 mA


Wattage equivalent	60 W
Starting time (nom.)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (nom.)	220-240 V
Temperature	
Ambient temperature range	-20°C to 45°C
T-Case maximum (nom.)	95 °C
Controls and dimming	
Dimmable	No
Mechanical and housing	
Lamp Finish	Frosted
Bulb material	Plastic
Bulb shape	A60 [A 60 mm]
Approval and application	
Energy Efficiency Class	F
Energy consumption kWh/1,000 hours	8 kWh
EPREL registration number	1211086
EU RoHS compliant	Yes

CorePro LEDbulb

Product data	
Full EOC	871951447660800
Order product name	CoreProLEDbulb ND 7.5-60W A60 B22 930 UK
Order code	47660800
SAP numerator – quantity per pack	1
Numerator – packs per outer box	10



Material number (12NC)	929003543899
Full product name	CoreProLEDbulb ND 7.5-60W A60 B22 930 UK
EAN/UPC – Case	8719514476615

Dimensional drawing




Product	D	C
CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	60 mm	105 mm

Photometric data



Light Distribution Diagram - CoreProLEDbulb ND 7.5-60W A60 B22 930 UK

General uniform lighting - CoreProLEDbulb ND 7.5-60W A60 B22 930 UK



Spectral Power Distribution Colour - CoreProLEDbulb ND 7.5-60W A60 B22 930 UK

CorePro LEDbulb

Lifetime



Life Expectancy Diagram - CoreProLEDbulb ND 7.5-60W A60 B22 930 UK



Lumen Maintenance Diagram - CoreProLEDbulb ND 7.5-60W A60 B22 930 UK

