


Data sheet | Item number: 2003-6692

End and intermediate plate; 0.8 mm thick; orange

www.wago.com/2003-6692



Data

Physical data

Width	0.8 mm / 0.031 inches
Height	110 mm / 4.331 inches
Depth	44.3 mm / 1.744 inches

Mechanical Data

Mounting type	snap-on type
---------------	--------------

Material Data

Note (material data)	Information on material specifications can be found here
Color	orange
Material group	I
Insulation material	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.099 MJ

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.

Weight	3.4 g
--------	-------

Commercial data

Product Group	22 (TOPJOB S)
eCl@ss 10.0	27-14-11-33
eCl@ss 9.0	27-14-11-33
ETIM 8.0	EC000886
ETIM 7.0	EC000886
PU (SPU)	100 (25) pcs
Packaging type	box
Country of origin	DE
GTIN	4050821322108
Customs tariff number	8538909990

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Required accessories

End plate

Multilevel installation terminal block



Item no.: 2003-6660

Multilevel installation terminal block; with operating slots; 2.5 mm²; Carrier terminal block without knife; P1/P2/PE; brown upper-deck; black middle-deck; green-yellow lower deck; Push-in CAGE CLAMP®; 2,50 mm²; gray

www.wago.com/2003-6660



Item no.: 2003-6640

Multilevel installation terminal block; with operating slots; 2.5 mm²; Carrier terminal block without knife; N/L/PE; Push-in CAGE CLAMP®; 2,50 mm²; gray

www.wago.com/2003-6640



Item no.: 2003-6641

Multilevel installation terminal block; with operating slots; 2.5 mm²; with pivoting knife disconnect; NTi/L /PE; Push-in CAGE CLAMP®; 2,50 mm²; gray

www.wago.com/2003-6641



Item no.: 2003-6642

Multilevel installation terminal block; with operating slots; 2.5 mm²; L/L; Push-in CAGE CLAMP®; 2,50 mm²; gray

www.wago.com/2003-6642



Item no.: 2003-6646

Multilevel installation terminal block; with operating slots; 2.5 mm²; N/L/PE; Push-in CAGE CLAMP®; 2,50 mm²; gray

www.wago.com/2003-6646



Item no.: 2003-6643

Multilevel installation terminal block; with operating slots; 2.5 mm²; Carrier terminal block without knife; P2/P1/PE; black upper deck; brown middle deck; green-yellow lower deck; Push-in CAGE CLAMP®; 2,50 mm²; gray

www.wago.com/2003-6643

Item no.: 2003-6644

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG

Hansastr. 27

32423 Minden

Phone: +49571 887-0 | Fax: +49571 887-169

Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?

We are always happy to take your call at +49 (571) 887-44222.



Multilevel installation terminal block; with operating slots; 2.5 mm²; with pivoting knife disconnect; LTi/L /PE; Push-in CAGE CLAMP®; 2,50 mm²; gray www.wago.com/2003-6644



Item no.: 2003-6645

Multilevel installation terminal block; with operating slots; 2.5 mm²; L/L/PE; Push-in CAGE CLAMP®; 2,50 mm²; gray www.wago.com/2003-6645



Item no.: 2003-6651

Multilevel installation terminal block; with operating slots; 2.5 mm²; N; Push-in CAGE CLAMP®; 2,50 mm²; gray www.wago.com/2003-6651



Item no.: 2003-6650

Multilevel installation terminal block; with operating slots; 2.5 mm²; L; Push-in CAGE CLAMP®; 2,50 mm²; gray www.wago.com/2003-6650



Item no.: 2003-6649

Multilevel installation terminal block; with operating slots; 2.5 mm²; N/L; Push-in CAGE CLAMP®; 2,50 mm²; gray www.wago.com/2003-6649



Item no.: 2003-6661

Multilevel installation terminal block; with operating slots; 2.5 mm²; Carrier terminal block without knife; L/N/PE; Push-in CAGE CLAMP®; 2,50 mm²; gray www.wago.com/2003-6661



Item no.: 2003-6662

Multilevel installation terminal block; with operating slots; 2.5 mm²; Carrier terminal block without knife; L/L/PE; green-yellow lower deck; Push-in CAGE CLAMP®; 2,50 mm²; gray www.wago.com/2003-6662

Downloads

Documentation

Bid Text

2003-6692 X81 - Datei	19 Feb 2019	xml 2.6 kB	Download
--------------------------	-------------	---------------	----------

2003-6692 doc - Datei	28 Apr 2017	doc 24.1 kB	Download
--------------------------	-------------	----------------	----------

Additional Information

		pdf 2.2 MB	Download
--	--	---------------	----------

CAD/CAE-Data

CAE data

WSCAD Universe 2003-6692		URL	Download
--------------------------	--	-----	----------

EPLAN Data Portal 2003-6692		URL	Download
-----------------------------	--	-----	----------

ZUKEN Portal 2003-6692

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG
 Hansastr. 27
 32423 Minden
 Phone: +49571 887-0 | Fax: +49571 887-169
 Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
 We are always happy to take your call at +49 (571) 887-44222.



[URL](#) [Download](#)

CAD data

2D/3D Models 2003-6692

[URL](#) [Download](#)

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 2003-6692
End and intermediate plate; 0.8 mm thick; orange

[URL](#) [Download](#)

Installation Notes

Product family

TOPJOB® S

TOPJOB® S: In various industrial applications and modern building installations, WAGO's wide and versatile range of rail-mount terminal blocks provides more than just reliable electrical connections.

[Show all products from the family](#)

Subject to changes. Please also observe the further product documentation!