


Data sheet | Item number: 2016-7692

End and intermediate plate; 1 mm thick; orange

www.wago.com/2016-7692



Color: 

Data

Physical data

Width	1 mm / 0.039 inches
Height	84.5 mm / 3.327 inches
Depth	41.7 mm / 1.642 inches

Mechanical Data

Mounting type	snap-on type
---------------	--------------

Material Data

Note (material data)	Information on material specifications can be found here
Color	orange
Material group	I
Insulation material	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.093 MJ
Weight	3.1 g

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.



Commercial data

Product Group	22 (TOPJOB S)
eCl@ss 10.0	27-14-11-33
eCl@ss 9.0	27-14-11-33
ETIM 8.0	EC000886
ETIM 7.0	EC000886
PU (SPU)	100 (25) pcs
Packaging type	box
Country of origin	DE
GTIN	4045454732318
Customs tariff number	85389099990

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Required accessories

End plate

Supply module	
	Item no.: 2016-7601 2-conductor supply terminal blocks for distribution boxes; 16 mm ² ; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 16,00 mm ² ; gray www.wago.com/2016-7601
	Item no.: 2016-7604 2-conductor supply terminal blocks for distribution boxes; 16 mm ² ; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 16,00 mm ² ; blue www.wago.com/2016-7604
	Item no.: 2016-7607 2-conductor ground terminal block; 16 mm ² ; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 16,00 mm ² ; green-yellow www.wago.com/2016-7607

Downloads

Documentation

Bid Text

2016-7692 X81 - Datei	19 Feb 2019	xml 2.6 kB	Download
2016-7692 doc - Datei	28 Apr 2017	doc 24.1 kB	Download

Additional Information

pdf Download

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG
 Hansastr. 27
 32423 Minden
 Phone: +49571 887-0 | Fax: +49571 887-169
 Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
 We are always happy to take your call at +49 (571) 887-44222.



2.2 MB

CAD/CAE-Data

CAE data

EPLAN Data Portal 2016-7692	URL	Download
WSCAD Universe 2016-7692	URL	Download
ZUKEN Portal 2016-7692	URL	Download

CAD data

2D/3D Models 2016-7692	URL	Download
------------------------	-----	----------

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 2016-7692	URL	Download
End and intermediate plate; 1 mm thick; orange		

Installation Notes

Product family

TOPJOB® S

TOPJOB® S: In various industrial applications and modern building installations, WAGO's wide and versatile range of rail-mount terminal blocks provides more than just reliable electrical connections.

[Show all products from the family](#)

Subject to changes. Please also observe the further product documentation!