

Data sheet | Item number: 2002-6391

End and intermediate plate; 0.8 mm thick; gray

www.wago.com/2002-6391



Data

Physical data

Width	0.8 mm / 0.031 inches
Height	52 mm / 2.047 inches
Depth	38.9 mm / 1.531 inches

Mechanical Data

Mounting type	snap-on type
---------------	--------------

Material Data

Note (material data)	Information on material specifications can be found here
Color	gray
Material group	I
Insulation material	Polyamide (PA66)
Flammability class per UL94	V0

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.

Fire load	0.044 MJ
Weight	1.4 g

Commercial data


Product Group	22 (TOPJOB S)
eCl@ss 10.0	27-14-11-33
eCl@ss 9.0	27-14-11-33
ETIM 8.0	EC000886
ETIM 7.0	EC000886
PU (SPU)	100 (25) pcs
Packaging type	box
Country of origin	DE
GTIN	4044918985970
Customs tariff number	85389099990

Environmental Product Compliance


RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Approvals / Certificates

Declarations of conformity and manufacturer's declarations

Logo	Approval	Additional Approval Text	Certificate name
	Railway WAGO GmbH & Co. KG	-	Railway Ready

Approvals for hazardous areas

Logo	Approval	Additional Approval Text	Certificate name
	IECEX Physikalisch Technische Bundesanstalt	IEC 60079	IECEX PTB 03.0004U (Ex eb IIC Gb or Ex eb I Mb)

Required accessories

End plate

Through terminal block

Subject to changes. Please also observe the further product documentation!



Item no.: 2002-6305

3-conductor through terminal block; 2.5 mm²; suitable for Ex e II applications; side and center marking; www.wago.com/2002-6305
for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; black



Item no.: 2002-6302

3-conductor through terminal block; 2.5 mm²; suitable for Ex e II applications; side and center marking; www.wago.com/2002-6302
for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; orange



Item no.: 2002-6303

3-conductor through terminal block; 2.5 mm²; suitable for Ex e II applications; side and center marking; www.wago.com/2002-6303
for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; red



Item no.: 2002-6405

4-conductor through terminal block; 2.5 mm²; suitable for Ex e II applications; side and center marking; www.wago.com/2002-6405
for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; black



Item no.: 2002-6304

3-conductor through terminal block; 2.5 mm²; for Ex e II and Ex i applications; side and center marking; www.wago.com/2002-6304
for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; blue



Item no.: 2002-6403

4-conductor through terminal block; 2.5 mm²; suitable for Ex e II applications; side and center marking; www.wago.com/2002-6403
for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; red



Item no.: 2002-6301

3-conductor through terminal block; 2.5 mm²; suitable for Ex e II applications; side and center marking; www.wago.com/2002-6301
for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; gray



Item no.: 2002-6402

4-conductor through terminal block; 2.5 mm²; suitable for Ex e II applications; side and center marking; www.wago.com/2002-6402
for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; orange



Item no.: 2002-6404

4-conductor through terminal block; 2.5 mm²; suitable for Ex e II applications; side and center marking; www.wago.com/2002-6404
for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; blue



Item no.: 2002-6401

4-conductor through terminal block; 2.5 mm²; suitable for Ex e II applications; side and center marking; www.wago.com/2002-6401
for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; gray



Item no.: 2002-6406

4-conductor through terminal block; 2.5 mm²; suitable for Ex e II applications; side and center marking; www.wago.com/2002-6406
for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; yellow



Item no.: 2002-6306

3-conductor through terminal block; 2.5 mm²; suitable for Ex e II applications; side and center marking; www.wago.com/2002-6306
for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; yellow

Item no.: 2202-6302

Subject to changes. Please also observe the further product documentation!



3-conductor through terminal block; with push-button; 2.5 mm²; suitable for Ex e II applications; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; orange

www.wago.com/2202-6302



Item no.: 2202-6301

3-conductor through terminal block; with push-button; 2.5 mm²; suitable for Ex e II applications; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; gray

www.wago.com/2202-6301



Item no.: 2202-6303

3-conductor through terminal block; with push-button; 2.5 mm²; suitable for Ex e II applications; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; red

www.wago.com/2202-6303



Item no.: 2202-6304

3-conductor through terminal block; with push-button; 2.5 mm²; for Ex e II and Ex i applications; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; blue

www.wago.com/2202-6304



Item no.: 2202-6306

3-conductor through terminal block; with push-button; 2.5 mm²; suitable for Ex e II applications; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; yellow

www.wago.com/2202-6306



Item no.: 2202-6401

4-conductor through terminal block; with push-button; 2.5 mm²; suitable for Ex e II applications; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; gray

www.wago.com/2202-6401



Item no.: 2202-6402

4-conductor through terminal block; with push-button; 2.5 mm²; suitable for Ex e II applications; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; orange

www.wago.com/2202-6402



Item no.: 2202-6403

4-conductor through terminal block; with push-button; 2.5 mm²; suitable for Ex e II applications; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; red

www.wago.com/2202-6403



Item no.: 2202-6404

4-conductor through terminal block; with push-button; 2.5 mm²; suitable for Ex e II applications; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; blue

www.wago.com/2202-6404



Item no.: 2202-6406

4-conductor through terminal block; with push-button; 2.5 mm²; suitable for Ex e II applications; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; yellow

www.wago.com/2202-6406

Shield terminal block

Item no.: 2002-6308

Subject to changes. Please also observe the further product documentation!



3-conductor shield terminal block; 2.5 mm²; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; white www.wago.com/2002-6308

Ground terminal block



Item no.: 2002-6307
3-conductor ground terminal block; 2.5 mm²; suitable for Ex e II applications; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; green-yellow www.wago.com/2002-6307



Item no.: 2002-6407
4-conductor ground terminal block; 2.5 mm²; suitable for Ex e II applications; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; green-yellow www.wago.com/2002-6407



Item no.: 2202-6307
3-conductor ground terminal block; with push-button; 2.5 mm²; suitable for Ex e II applications; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; green-yellow www.wago.com/2202-6307



Item no.: 2202-6407
4-conductor ground terminal block; with push-button; 2.5 mm²; suitable for Ex e II applications; side and center marking; for DIN-rail 35 x 15 and 35 x 7.5; Push-in CAGE CLAMP®; 2,50 mm²; green-yellow www.wago.com/2202-6407

Downloads

Documentation

Bid Text

2002-6391 X81 - Datei	19 Feb 2019	xml 2.6 kB	Download
--------------------------	-------------	---------------	----------

2002-6391 doc - Datei	27 Apr 2017	doc 24.1 kB	Download
--------------------------	-------------	----------------	----------

Additional Information

		pdf 2.2 MB	Download
--	--	---------------	----------

CAD/CAE-Data

CAD data

2D/3D Models 2002-6391		URL	Download
------------------------	--	-----	----------

CAE data

EPLAN Data Portal 2002-6391		URL	Download
-----------------------------	--	-----	----------

Subject to changes. Please also observe the further product documentation!



WSCAD Universe 2002-6391	URL	Download
ZUKEN Portal 2002-6391	URL	Download

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 2002-6391 End and intermediate plate; 0.8 mm thick; gray	URL	Download
--	---------------------	--------------------------

Installation Notes

Product family

TOPJOB® S

TOPJOB® S: In various industrial applications and modern building installations, WAGO's wide and versatile range of rail-mount terminal blocks provides more than just reliable electrical connections.

[Show all products from the family](#)

Subject to changes. Please also observe the further product documentation!