

## Product information

# 00 21 21 HK S

## Plumber's tool case

52 parts












- Equipped with 52 brand quality tools, some VDE tested according to DIN EN 60900
- Max. payload: 20 kg
- Volume: 27 litres
- For extensive plumbing and installation work
- Flexible options due to the individual partitioning of the inserts in the 60 mm deep base tray and its cover plate with six large tool compartments
- Tough ratchet hinges hold the lid open where necessary despite the deadweight of the tools
- Sturdy, ergonomic carrying handle, snaps into place at a 90° angle
- Removable tool board with 15 tool pockets on the base side and six tool pockets as well as a clamp compartment (400 mm wide) on the cover side, held by a push button
- Two lockable steel flip locks protect the case contents from theft
- With circumferential double aluminium frame
- Heavy duty ABS material, black
- Cover and tool boards made from dirt-repellent PP twin-wall sheets
- External dimensions (W x H x D): 480 x 380 x 200 mm; internal dimensions (W x H x D): 460 x 310 x 190 mm

### General

Article No.	00 21 21 HK S
EAN	4003773080671
Weight	9,600 g
Dimensions	170 x 340 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Content

00 11 01	1 x KNIPEX TwinKey® for all standard cabinets and shut-off systems
26 16 200	1 x Snipe Nose Side Cutting Pliers (Stork Beak Pliers) ⚠️ 1000V   
74 06 180	1 x High Leverage Diagonal Cutter ⚠️ 1000V 
86 03 250	1 x Pliers Wrench pliers and a wrench in a single tool 
87 01 250	1 x KNIPEX Cobra® High-Tech Water Pump Pliers 
87 01 400	1 x KNIPEX Cobra® XL Pipe Wrench and Water Pump Pliers 
87 01 400	1 x KNIPEX Cobra® XL Pipe Wrench and Water Pump Pliers 
87 01 400	1 x KNIPEX Cobra® XL Pipe Wrench and Water Pump Pliers 
16640003	1 x Heyco Safety cutter knife (18 mm)
90958	1 x Heyco Express key ( M 10)
101-0300	1 x Picard Locksmith's hammer (300 g)

Content	
340 250 1	1 x Rennsteig Mason's Chisels (250 mm)
2281	1 x Stabila spirit level type 70 (30 cm)
0022086	1 x Wera set of hex key wrenches (1,5 - 10 mm)
003760	1 x Wera Joker open-end wrench (10 x 13 mm)
004018	1 x Wera 8100 SA 8 Zyklop set of metal ratchets 28 parts (1/4")
005655	1 x Wera Voltage detector, single-pole 247 (0,5 x 3,0 x 70 mm)
006110	1 x Wera Screwdrivers for slotted screws 160i
006152	1 x Wera Screwdrivers for cross recessed Phillips® screws 162i PH (PH1 x 80 mm) ⚠ 1000V ⚡
006154	1 x Wera Screwdrivers for cross recessed Phillips® screws 162i PH (PH2 x 100 mm)
18266	1 x Wera Slotted chisel 932 A (1,2 x 7,0 x 125)
18268	1 x Wera Slotted chisel 932 A (1,6 x 9,0 x 150)
6120	1 x Wera Screwdrivers for slotted screws 160i (1,0 x 5,5 x 125 mm)
6172	1 x Wera 167 i (TX15)
6174	1 x Wera 167 i (TX20)
6176	1 x Wera 167 i (TX25)

*technical change and errors excepted*

*Con-Pearl® is a registered trade mark of friedola TECH GmbH*