



CorePro LEDbulb

CoreProLEDbulb ND 7.5-60W A60 B22 930 UK

LEDbulbs are compatible with existing fixtures with an E27 holder and are designed for retrofit replacement of incandescent bulbs.

Product data


General information		Starting time (nom.)	
Lighting Technology	LED		0.5 s
Switching Cycle	50,000	Warm-up time to 60% light	0.5 s
Nominal lifetime	15,000 h	Power Factor (Fraction)	0.5
Cap base	B22 [B22]	Voltage (nom.)	220-240 V
Light technical		Temperature	
Colour Code	930 [CCT of 3000K]	T-Case maximum (nom.)	98 °C
Beam angle (nom.)	200 degree(s)	Controls and dimming	
Luminous Flux	806 lm	Dimmable	No
Colour designation	White (WH)	Mechanical and housing	
Correlated Colour Temperature	3000 K	Lamp Finish	Frosted
Luminous Efficacy (rated) (Nom)	107 lm/W	Bulb shape	A60 [A 60 mm]
Colour consistency	<6	Approval and application	
Colour rendering index (CRI)	90	Energy Efficiency Class	F
LLMF at end of nominal lifetime (nom.)	70 %	Energy consumption kWh/1,000 hours	8 kWh
Flickering value (PstLM)	0.1	EPREL registration number	438121
Stroboscopic effect	0.4	EU RoHS compliant	Yes
Operating and electrical		Product data	
Line Frequency	50 to 60 Hz	Full EOC	871951432974401
Input frequency	50 to 60 Hz	Order product name	CoreProLEDbulb ND 7.5-60W A60 B22 930 UK
Power Consumption	7.5 W	Order code	32974401
Lamp current (nom.)	66 mA		
Wattage equivalent	60 W		

CorePro LEDbulb

SAP numerator – quantity per pack	1
Numerator – packs per outer box	10
Material number (12NC)	929003002499
Full product name	CoreProLEDbulb ND 7.5-60W A60 B22 930 UK



EAN/UPC - Case	8719514405370
----------------	---------------

Dimensional drawing




Product	D	C
CoreProLEDbulb ND 7.5-60W A60 B22 930 UK	60 mm	110 mm

Photometric data



Spectral Power Distribution Colour


Light Distribution Diagram - CoreProLEDbulb ND 7.5-60W A60 B22 930 UK



General uniform lighting - CoreProLEDbulb ND 7.5-60W A60 B22 930 UK

CorePro LEDbulb

Lifetime



Life Expectancy Diagram - CoreProLEDbulb ND 7.5-60W A60 B22 930 UK

Lumen Maintenance Diagram - CoreProLEDbulb ND 7.5-60W A60 B22 930 UK

