



Part Number : [500798100](#)

Product Description : 1.25mm Pitch,
PicoBlade Female Crimp Terminal, Tin (Sn)
Plating, 26-28 AWG, Bag

Series Number : 50079

Status : New Business Not Supported

Product Category : Crimp Terminals


Packaging Alternative : [0500798000](#) (Reel)



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	New Business Not Supported
Category	Crimp Terminals
Series	50079
Description	1.25mm Pitch, PicoBlade Female Crimp Terminal, Tin (Sn) Plating, 26-28 AWG, Bag
Application	Signal, Wire-to-Board, Wire-to-Wire
Product Family	PicoBlade Connector System
Product Name	PicoBlade
UPC	800753749740

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	125V AC (RMS)/DC

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	9.911/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.04mm max.
Wire Size (AWG)	26, 28
Wire Size mm ²	N/A

Application Tooling

Global

Description	Part Number
Extraction Tool for Micro-Fit Terminals	<u>0011030043</u>
Hand Crimp Tool for 1.25mm Pitch PicoBlade Receptacle Crimp Terminals, 26-32 AWG	<u>2002181900</u>
Hand Crimper	<u>0638110300</u>
Hand Crimp Tool for 1.25mm Pitch Crimp Terminals, 26-32 AWG Wire	<u>0638190300</u>
Hand Crimp Tool for 1.25mm Pitch Crimp Terminals, 26-32 AWG Wire	<u>0638190400</u>
Hand Crimp Tool	<u>0638257000</u>
Hand Crimp Tool for 1.25mm Pitch PicoBlade Female Crimp Terminals, 26-32 AWG	<u>0638271400</u>

Application Tooling

Japan

Description	Part Number
Extraction Tool	<u>0570726000</u>
Hand Crimp Tool	<u>0571775000</u>