

Product information

00 21 06 HL S

Tool Case "BIG Basic Move" Electric











- Equipped with six KNIPEX tools, a total of 24 brand tools, partly VDE-tested according to DIN EN 60900
- Telescopic handle set in the base as well as two external, smooth-running skater wheels
- Two metal flip locks and a three-digit combination lock for secure locking of the cover
- Label field with two stickers for individual labelling
- Max. payload: 20 kg
- Volume: 33 litres
- Strong, ergonomic handle
- Heavy duty ABS material, black
- Circumferential aluminium frame
- Metal hinges
- Document compartment in the cover
- Two removable tool boards made of dirt-repellent PP twin-fall sheets with 31 tool pockets
- First tool board with ten tool pockets and an elastic strap on the cover side and eleven narrow and one large tool pocket on the base side
- Second tool board with ten tool pockets and an elastic strap on the base side and a document compartment on the cover side
- Base tray, can be fixed by a push button, 70 mm high, can be subdivided by inserts, cover board with 14 large tool pockets
- With a total of 54 inserting options



General	
Article No.	00 21 06 HL S
EAN	4003773084235
Weight	10,425 g
Dimensions	269 x 439 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Dimension exterior (interior) width mm	430 mm (350 mm)
Dimension exterior (interior) height mm	280 mm (200 mm)
Dimension exterior (interior) depth mm	515 mm (480 mm)

Content	
03 06 180	1 x Combination Pliers ⚠ 1000V  
11 06 160	1 x Insulation Stripper with opening spring, universal (Ø 5,0 mm / 10,0 mm ²) ⚠ 1000V 
16 20 165 SB	1 x Dismantling Tool with scalpel blade (Ø 8,0 – 28,0 mm) 
26 16 200	1 x Snipe Nose Side Cutting Pliers (Stork Beak Pliers) ⚠ 1000V   
70 06 160	1 x Diagonal Cutter ⚠ 1000V 
98 52	1 x Cable Knife ⚠ 1000V
306125	1 x Haunstetter PUK® Junior Hacksaw (150 x 240 mm)

Content	
3185-04	1 x Maurerfreund Painter's spatula 40 mm, wood, high quality (40 mm)
75040-015	1 x Picard Flat brush (40 mm)
75063-000	1 x Picard Plaster bowl (127 x 94)
340 250 1	1 x Rennsteig Mason's Chisels (250 mm)
361 252 1	1 x Rennsteig Electrician's Chisel (250 x 10 mm)
3003010119	1 x Ruthe Locksmith's hammer, 300 g (300 g)
3010030119	1 x Ruthe Sledge hammer (1000 g)
15212	1 x Stabila Carpenter's pencil
005655	1 x Wera Voltage detector, single-pole 247 (0,5 x 3,0 x 70 mm)
031580	1 x Wera Screwdrivers for slotted screws 1160i (0,4 x 2,5 x 80 mm)
031582	1 x Wera Screwdrivers for slotted screws 1160i (0,6 x 3,5 x 100 mm)
031587	1 x Wera Screwdrivers for slotted screws 1160i (1,0 x 5,5 x 125 mm)
031588	1 x Wera Screwdrivers for slotted screws 1160i (1,2 x 6,5 x 150 mm)
031601	1 x Wera Screwdrivers for cross recessed Phillips® screws 1162i (PH1 x 80 mm)
031603	1 x Wera Screwdrivers for cross recessed Phillips® screws 1162i (PH2 x 100 mm)
31611	1 x Wera Screwdrivers for cross recessed Pozidriv® screws 1165i (PZ1 x 80 mm)
31613	1 x Wera Screwdrivers for cross recessed Pozidriv® screws 1165i (PZ2 x 100 mm)
Accessories	
00 21 06 LE	Tool Case "BIG Basic Move" empty,

technical change and errors excepted