

Data sheet | Item number: 770-101

Locking lever; for flying leads; for manual operation; black

www.wago.com/770-101



Color:

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.



Item description

Locking system *WINSTA*® MIDI

Choose tried-and-tested sustainability for the electrical installation in your project: The locking system from the *WINSTA*® MIDI product line. An extensive range of accessories complements the *WINSTA*® product line from WAGO. *WINSTA*® MIDI with Push-in CAGE CLAMP® spring pressure connection technology is used in can be found in a variety of projects you can use for quick, easy and maximally flexible electrical installation.

WINSTA® MIDI solutions for your electrical installation – maintenance-free

WINSTA® is the pluggable connection system that is perfectly tailored to the strict requirements of electrical installation. It offers error-free installation of cables and components, quickly and reliably. Enjoy the benefits of the pluggable version of our maintenance-free spring pressure connection technology too! Plan your installation with *WINSTA*® MIDI accessories from WAGO.

-
- simple circuits
- quick replacement of defective units during ongoing operation

Data

Connection data

Connection 1

Actuation type	Finger-operated lever
----------------	-----------------------

Mechanical Data

Suitable	for flying leads; manually operated
----------	-------------------------------------

Material Data

Note (material data)	Information on material specifications can be found here
----------------------	--

Color	black
-------	-------

Insulation material	Polyamide (PA66)
---------------------	------------------

Flammability class per UL94	V0
-----------------------------	----

Subject to changes. Please also observe the further product documentation!

WAGO GmbH & Co. KG
Hansastr. 27
32423 Minden
Phone: +49571 887-0 | Fax: +49571 887-169
Email: info.de@wago.com | Web: www.wago.com

Do you have any questions about our products?
We are always happy to take your call at +49 (571) 887-44222.



Fire load	0.022 MJ
Weight	0.6 g

Environmental requirements

Processing temperature	-5 ... +40 °C
Continuous operating temperature	-35 ... +85 °C
Note on continuous operating temperature	Insulating parts for temperatures ≤ 105 °C

Commercial data

Product Group	20 (Winsta)
eCl@ss 10.0	27-44-06-92
eCl@ss 9.0	27-44-06-92
ETIM 8.0	EC002863
ETIM 7.0	EC002863
PU (SPU)	100 (25) pcs
Packaging type	box
Country of origin	DE
GTIN	4017332660907
Customs tariff number	85389099990

Environmental Product Compliance

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Approvals / Certificates

General approvals

Logo	Approval	Additional Approval Text	Certificate name
	VDE VDE Prüf- und Zertifizierungsinstitut	EN 61535	40029808

Downloads

Documentation

Bid Text

770-101	19 Feb 2019	xml	Download
X81 - Datei		2.7 kB	

Subject to changes. Please also observe the further product documentation!



770-101	11 Mar 2015	doc	Download
doc - Datei		22.0 kB	

CAD/CAE-Data

CAD data

2D/3D Models 770-101	URL	Download
----------------------	-----	----------

CAE data

WSCAD Universe 770-101	URL	Download
------------------------	-----	----------

ZUKEN Portal 770-101	URL	Download
----------------------	-----	----------

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 770-101	URL	Download
--	-----	----------

Locking lever; for flying leads; for manual operation; black

Installation Notes

Product family

WINSTA® MIDI

[Show all products from the family](#)

Subject to changes. Please also observe the further product documentation!